



General Specifications

Nominal Diameter	10 Inch
Rated Impedance	8Ω
Operating Bandwidth	35-4k Hz (±3dB)
Max Power Handling Capacity	200 Watts
Rms Power Handling Capacity	60 Watts
Sensitivity (1W/M)	87dB (±3dB)
Voice Coil Diameter	1.5 Inch


Thieve-Small Parameters

Resonance Frequency	Fs:	37Hz ±20%
DC Resistance	Re:	3.4Ω ±10%
Mechanical Q Factor	Qms:	3.5558 ±15%
Electrical Q Factor	Qes:	0.9858 ±15%
Total Q Factor	Qts:	0.7718 ±15%
Equivalent Cas air load	Vas:	61.2 L ±15%
Surface Area of Cone	Sd:	3.530m2 ±15%
Efficiency Bandwidth Product	EBP	37.5 ±15%
Voice Coil Over Hang	X-max	6.2mm

Physical Information



Basket	Steel
Magnet Type	24 OZ ±5%
Cone Material	Black PP Cone
Surround	Rubber
Dust Cap	PP
Damper	Cloth

Diagram



Dimensions : Millimetres

Curve Data



Part Number Table

Description	Part Number
Woofer with Polypropelyne Cone and Rubber Surround, 10", 4Ω, 50Hz - 5kHz, 100W, 90dB	55-3232

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.