



# Touch panel screen, Harmony ST6 & STW6, 4"W display, 1Ethernet, USB host&device, 24 VDC

HMISTW6200

EAN Code: 3606489918071

#### Main

Range of product	Harmony ST6			
Product or component type	Touch panel screen			
Software designation	Web interface for operator			
Processor name	ARM Cortex-A8			
Processor frequency	800 MHz			
Memory description	512 MB device memory 512 MB user data memory 128 kB backup memory			

# Complementary

Display size	4 inch				
Display type	Colour TFT LCD				
Display colour	16 million colours				
Display resolution	480 x 272 pixels				
Touch panel	Single touch analogue resistive				
Backlight lifespan	50000 hours with white				
Brightness	16 levels				
Character font	ASCII ASCII (European characters) Katakana				
[Us] rated supply voltage	24 V DC (+/- 20 %)				
Power consumption in W	6.9 W				
Inrush current	30 A				
Local signalling	Status LED green, steady for offline Status LED green, steady for operating Status LED green, flashing for operating Status LED green, faded for stand-by Status LED orange, flashing for software starting up Status LED red, steady for power supply (ON) Status LED red, flashing for operating Status LED red, off for power supply (OFF)				
Port Ethernet	10/100BASE				
Integrated connection type	1 USB 2.0 type Aback 1 Ethernet - female RJ45bottom				
Supply	External supply				
Realtime clock	Built-in 050 °C Built-in 1090 % RH				

Fixing mode	By 2 screws, mounting on 1.65 mm thick panel conforming to UL 61010-2-201 By 2 screws conforming to IEC 61131-2 By 2 screws conforming to IEC 61000-6-2				
Enclosure material	PC				
Front material	Aluminium				
Marking	CE				
Cut-out dimensions	118.5 x 92.5 mm panel cut dimension				
Height	108.5 mm				
Width	134.5 mm				
Depth	43 mm				
Net weight	0.4 kg				

# **Environment**

Immunity to microbreaks	2 ms				
	IEC 61000-6-4				
	IEC 61000-6-2				
	IEC 61131-2				
	UL 61010-2-201				
	CSA C22.2 No 61010-2-201				
Product certifications	CSA				
	CE				
	UKCA				
Directives	2014/35/EU - low voltage directive				
	2014/30/EU - electromagnetic compatibility				
Ambient air temperature for operation	050 °C				
Ambient air temperature for storage	-2060 °C				
Relative humidity	1090 % non-condensing				
Operating altitude	2000 m				
IP degree of protection	IP20 (rear panel) conforming to IEC 61131-2				
	IP65 (front panel) conforming to IEC 61131-2				
NEMA degree of protection	NEMA 4 front panel (indoor use)				
	NEMA 13 front panel (in enclosure)				
Shock resistance	147 m/s² for 11 ms (X, Y, Z directions for 10 cycles (approx. 100 min)) conforming to				
	IEC 61131-2				
Vibration resistance	+/- 3.5 mm (f = 59 Hz) X, Y, Z directions for 10 cycles (approx. 100 min)				
	conforming to IEC 61131-2				
	9.8 m/s <sup>2</sup> (f = 9150 Hz)				
Electromagnetic compatibility	Electrical fast transient/burst immunity test - test level: 2 kV (power ports) conforming				
	to IEC 61000-4-4				
	Electrical fast transient/burst immunity test - test level: 1 kV (signal ports)				
	Electrostatic discharge immunity test - test level: 6 kV (contact discharge) conforming				
	to IEC 61000-4-2 level 3				
	Electrostatic discharge immunity test - test level: 8 kV (air discharge)				

# **Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.8 cm
Package 1 Width	18.2 cm
Package 1 Length	13.2 cm

Package 1 Weight	446.0 g
Unit Type of Package 2	S03
Number of Units in Package 2	12
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	5.352 kg
Unit Type of Package 3	P12
Number of Units in Package 3	384
Package 3 Height	135.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	187.04 kg

# **Contractual warranty**

Warranty 18 months

# Sustainability Green Premium

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance



Mercury Free



Rohs Exemption Information

Yes

## **Certifications & Standards**


Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

24 Oct 2024

#### **Dimensions Drawings**

#### **Dimensions**


#### **External Dimensions**



(1) : Front (2) : Left

(3) : Bottom


#### **Dimensions with Installation Fasteners**



(1) : Front (2) : Left (3) : Bottom


## **Dimensions with Spring Clips**

## HMISTW6200



(1) : Front (2) : Left (3) : Bottom

#### **Dimensions with Cables**




(1) : Rear (2) : Right

# HMISTW6200

Mounting and Clearance


## Mounting

#### **Panel Cut Dimensions**




Α		В		C Installing with spring			
				Position 1		Position 2	
mm	in.	mm	in.	mm	in.	mm	in.
118.5 (+1, -0)	4.67 (+0.04, -0)	92.5 (+1, -0)	3.64 (+0.04, -0)	1.54	0.060.16	46	0.160.24

## **Installation Requirements**




- 1 : Internal temperature
- 2 : External temperature



1 : Power connector


## **Mounting Angle**



#### Clearance


# **Product datasheet**

# HMISTW6200



Offer Marketing Illustration

#### **Product benefits / Features**




Offer Marketing Illustration

#### **Product benefits / Features**

# **Technical Benefits**

#### Harmony ST6 Web HMI



11

Image of product / Alternate images

#### **Alternative**



