


Category 6A Shielded Keystone Panel Mount Coupler



Category 6A Shielded Keystone Panel Mount Coupler (SGACK2S, SGACK2S#24)

Features:

- Designed to fit US industry standard keystone outlets, wall plates and patch panels
- RJ45 complies with FCC part 68 standard
- Jack insertion life > 750 mating cycles
- Operating temperature: -40°C ~ +60°C
- High performance data throughput Category 6A, ANSI/TIA/EIA-568-B.2-10 – can run 10GBASE-T at 100 metres
- Compliant with IEEE standard for PoE+ and 4PPoE IEEE 802.3
- Available as part of our innovative Panel Mount and D UNIVERSAL ranges

Specifications:

- **Materials**
Housing: Nickel plated zinc alloy
Earthing lug material: Stainless steel SUS304
Contacts: 50µ"/1.27µm gold plated over nickel over phosphor bronze
- **Weight:**
SGACK2S: 17g SGACK2S#24: 410g
- **Dimensions:**
SGACK2S: 29.7 x 17 x 19.25 mm approx.
SGACK2S-24: 282 x 70 x 35mm approx

Packaging:

- Standard product is supplied in individual polythene bags then in bags of 20. To save time for panel assemblers, SGACK2S-24 is available as a bulk-pack of 24 pieces without individual bags.

EAN:

SGACK2S: 5055386510426




SGACK2S#24: 5055386505262

Commodity code: 85369010

Country of Origin: China

ROHS Compliant

Code: SGACK2S



ELECTRICAL:

Current Rating : 1.5A
 Dielectric Withstanding Voltage : 1000V/AC 60Hz
 Insulation Resistance : 500 MΩ MIN.
 Contact Resistance : 20 mΩ MAX.

MECHANICAL:

Durability: RJ45 With 750 Mating Cycles
 and RJ11 With 200 Mating Cycles
 Supporting Cable Diameter: 6~9mm
 Operating Temperature: -10°C to +60°C
 Storage Temperature: -40°C to +70°C

MATERIAL:

Dust cap: PP
 Ground Lug: SUS304
 Front cover: Zn alloy + Nickel Plated
 LATCH: PC 94VO
 Bottom cover: Zn alloy + Nickel Plated

