


Specifications



Characteristics	PEL00796	PEL00797
Input Voltage	220V to 240V, ~50Hz	220V to 240V, ~50Hz
Power Consumption	6W	8W
Number of LEDs	30	60
Luminous Flux	455lm	560lm
Lifetime	30000 hours	30000 hours
Switching Cycles	15000	15000
Colour Temperature	6500k	6500k
CRI	≥80	≥80
Start Time	Instant full Light	Instant full Light
Magnifier Lens (Ø)	100mm (4")	125mm (5")
Magnification	1.17×(3 dioptré)	1.17×(3 dioptré)
Weight	1.3kgs	2.8kgs

Diagram of PEL00797



Part Number Table

Description	Part Number
4" LED Desk Magnifier Lamp, 30 LEDs	PEL00796
5" LED Magnifier Lamp, 60 LEDs	PEL00797

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-ELEC is the registered trademark of Premier Farnell Limited 2019.