






STRIPPING DIMENSIONS



Plating	Part no.
⑥ GOLD FLASH over min. 50µin NICKEL	16-000693
min. 30µin HARD GOLD over min. 50µin NICKEL	16-000691
min. 50µin HARD GOLD over min. 50µin NICKEL	16-000694

⑥ NOTES:

- MATERIAL: CONTACT: COPPER ALLOY (UNS) C19160
SLEEVE: STAINLESS STEEL
- CRIMPING: USE CRIMP TOOL 360X10329X
WITH TOOL INSERT 360X10629X
SELECTOR SETTINGS: 4 for AWG 22
3 for AWG 24
2 for AWG 26
1 for AWG 28

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

finish:				tolerance		
SEE TABLE						
					date	name
				drawn	20.08.08	Sonnenberg
				appd.	20.08.08	Kühle
				norm		
				d-old		
2 x b	Ä 4113	22.09.2011	Lehm.			
a	Original					
rev.	description	date	name			

CONEC®

scale:		10:1
material:		SEE NOTES
title:		
HD SOCKET CRIMP CONTACT for AWG 22 - 28		
dwg no:	Inventor 10	DIN-A3
	16K1A2301	sh: 1
part no:		SEE TABLE