



Safety Data Sheet

acc. to GB REACH

362 HMP 5C 1.2MM S

Version number: GHS 1.0

Date of compilation: 2024-11-20

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Trade name **362 HMP 5C 1.2MM S**
Alternative number(s) 290715

1.2 Relevant identified uses of the substance or mixture and uses advised against

Relevant identified uses industrial use

1.3 Details of the supplier of the safety data sheet

HARIMATEC CZECH s.r.o.
PointPark Prague D8, Hala DC03, Zdibsko 614
250 67 Klecany
Czech Republic

Telephone: +420 284 688 922
e-mail: sds-cz@harimagroup.com
Website: <https://www.harimatec.eu>

e-mail (competent person) lucie.dolska@harimagroup.com (Lucie Dolská)

1.4 Emergency telephone number

Emergency information service 24 Hours Emergency Tel: +44 (0)1442 278497

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

Classification acc. to GHS

Section	Hazard class	Category	Hazard class and category	Hazard statement
3.7	reproductive toxicity	1A	Repr. 1A	H360FD
3.7L	effects on or via lactation	L	Lact.	H362
3.9	specific target organ toxicity - repeated exposure	1	STOT RE 1	H372

For full text of abbreviations: see SECTION 16.

The most important adverse physicochemical, human health and environmental effects
Delayed or immediate effects can be expected after short or long-term exposure.

2.2 Label elements

Labelling

- Signal word danger

- Pictograms

GHS08





Safety Data Sheet

acc. to GB REACH

362 HMP 5C 1.2MM S

Version number: GHS 1.0

Date of compilation: 2024-11-20

- Hazard statements

H360FD May damage fertility. May damage the unborn child.
H362 May cause harm to breast-fed children.
H372 Causes damage to organs through prolonged or repeated exposure.

- Precautionary statements

P201 Obtain special instructions before use.
P261 Avoid breathing dust/fume/gas/mist/vapours/spray.
P263 Avoid contact during pregnancy and while nursing.
P280 Wear protective gloves/protective clothing/eye protection/face protection/hearing protection/....
P308+P313 IF exposed or concerned: Get medical advice/attention.

- Hazardous ingredients for labelling Lead

2.3 Other hazards

Results of PBT and vPvB assessment

Does not contain a PBT-/vPvB-substance at a concentration of $\geq 0,1\%$.

Endocrine disrupting properties

Does not contain an endocrine disruptor (ED) at a concentration of $\geq 0,1\%$.

SECTION 3: Composition/information on ingredients

3.1 Substances

Not relevant (mixture)

3.2 Mixtures

Description of the mixture

Name of substance	Identifier	Wt%	Classification acc. to GHS	Pictograms
Lead	CAS No 7439-92-1 EC No 231-100-4 Index No 082-013-00-1	≥ 90	Repr. 1A / H360FD Lact. / H362 STOT RE 1 / H372	
Silver	CAS No 7440-22-4 EC No 231-131-3	1 – < 5	Aquatic Acute 1 / H400 Aquatic Chronic 1 / H410	

Name of substance	Specific Conc. Limits	M-Factors	ATE	Exposure route
Lead	Repr. 1A; H360D: C $\geq 0.03\%$	-	-	
Silver	-	M-factor (acute) = 1,000	-	



Safety Data Sheet

acc. to GB REACH

362 HMP 5C 1.2MM S

Version number: GHS 1.0

Date of compilation: 2024-11-20

Name of substance	Specific Conc. Limits	M-Factors	ATE	Exposure route
		M-factor (chronic) = 10		

Remarks

For full text of abbreviations: see SECTION 16

SECTION 4: First aid measures

4.1 Description of first aid measures

General notes

Do not leave affected person unattended. Remove victim out of the danger area. Keep affected person warm, still and covered. Take off immediately all contaminated clothing. In all cases of doubt, or when symptoms persist, seek medical advice. In case of unconsciousness place person in the recovery position. Never give anything by mouth.

Following inhalation

If breathing is irregular or stopped, immediately seek medical assistance and start first aid actions. Provide fresh air.

Following skin contact

Brush off loose particles from skin. Rinse skin with water/shower.

Following eye contact

Remove contact lenses, if present and easy to do. Continue rinsing. Irrigate copiously with clean, fresh water for at least 10 minutes, holding the eyelids apart.

Following ingestion

Rinse mouth with water (only if the person is conscious). Do NOT induce vomiting.

4.2 Most important symptoms and effects, both acute and delayed

Symptoms and effects are not known to date.

4.3 Indication of any immediate medical attention and special treatment needed

none

SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing media

Water, Foam, ABC-powder

Unsuitable extinguishing media

Water jet

5.2 Special hazards arising from the substance or mixture

5.3 Advice for firefighters

In case of fire and/or explosion do not breathe fumes. Co-ordinate firefighting measures to the fire surroundings. Do not allow firefighting water to enter drains or water courses. Collect contaminated firefighting water separately. Fight fire with normal precautions from a reasonable distance.



Safety Data Sheet

acc. to GB REACH

362 HMP 5C 1.2MM S

Version number: GHS 1.0

Date of compilation: 2024-11-20

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

For non-emergency personnel

Remove persons to safety.

For emergency responders

Wear breathing apparatus if exposed to vapours/dust/spray/gases.

6.2 Environmental precautions

Keep away from drains, surface and ground water. Retain contaminated washing water and dispose of it.

6.3 Methods and material for containment and cleaning up

Advice on how to contain a spill

Covering of drains, Take up mechanically

Advice on how to clean up a spill

Take up mechanically.

Other information relating to spills and releases

Place in appropriate containers for disposal. Ventilate affected area.

6.4 Reference to other sections

Personal protective equipment: see section 8. Incompatible materials: see section 10. Disposal considerations: see section 13.

SECTION 7: Handling and storage

7.1 Precautions for safe handling

Recommendations

- Measures to prevent fire as well as aerosol and dust generation

Use local and general ventilation. Take precautionary measures against static discharge. Use only in well-ventilated areas. Ground/bond container and receiving equipment.

- Specific notes/details

Dust deposits may accumulate on all deposition surfaces in a technical room. The product in the delivered form is not dust explosion capable; the enrichment of fine dust however leads to the danger of dust explosion.

Advice on general occupational hygiene

Wash hands after use. Do not eat, drink and smoke in work areas. Remove contaminated clothing and protective equipment before entering eating areas. Never keep food or drink in the vicinity of chemicals. Never place chemicals in containers that are normally used for food or drink. Keep away from food, drink and animal feedingstuffs.

7.2 Conditions for safe storage, including any incompatibilities

Managing of associated risks

- Explosive atmospheres

Removal of dust deposits.

- Ventilation requirements

Use local and general ventilation.

7.3 Specific end use(s)

See section 16 for a general overview.



Safety Data Sheet

acc. to GB REACH

362 HMP 5C 1.2MM S

Version number: GHS 1.0

Date of compilation: 2024-11-20

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Occupational exposure limit values (Workplace Exposure Limits)											
Country	Name of agent	CAS No	Identifier	TWA [ppm]	TWA [mg/m ³]	STEL [ppm]	STEL [mg/m ³]	Ceiling-C [ppm]	Ceiling-C [mg/m ³]	Notation	Source
GB	dust		WEL		10					i	EH40/2005
GB	dust		WEL		4					r	EH40/2005
GB	lead	7439-92-1	OEL		0.15						CLWR
GB	silver	7440-22-4	WEL		0.1						EH40/2005

Notation

Ceiling-C ceiling value is a limit value above which exposure should not occur

i inhalable fraction

r respirable fraction

STEL short-term exposure limit: a limit value above which exposure should not occur and which is related to a 15-minute period (unless otherwise specified)

TWA time-weighted average (long-term exposure limit); measured or calculated in relation to a reference period of 8 hours
time-weighted average (unless otherwise specified)

Biological limit values						
Country	Name of agent	Parameter	Notation	Identifier	Value	Source
GB	lead	lead	Pb-bio-2, Pb-med-2, wmn<45y	AL	250 µg/l	CLWR
GB	lead	lead	Pb-bio-2, Pb-med-3, wmn>45y, men	AL	400 µg/l	CLWR
GB	lead	lead	Pb-bio-2, Pb-med-4, young	AL	500 µg/l	CLWR

Notation

Pb-bio-2 biological monitoring: (a) in respect of a worker other than a young person or a woman of reproductive capacity, at least every 6 months, but where the results of the measurements for individuals or for groups of workers have shown on the previous two consecutive occasions on which monitoring was carried out a lead in air exposure greater than 0.075 mg/m³ but less than 0.100 mg/m³ and where the blood-lead concentration of any individual worker is less than 30 µg/dl, the frequency of monitoring may be reduced to once a year; or (b) in respect of any young person or a woman of reproductive capacity, at such intervals as the relevant doctor shall specify, being not greater than 3 months

Pb-med-2 medical surveillance: in respect of a woman of reproductive capacity, 20 g/dl (blood-lead concentration) or 20 g Pb/g creatinine (urinary lead concentration)

Pb-med-3 medical surveillance: in respect of any other worker, 35 µg/dl (blood-lead concentration) or 40 µg Pb/g creatinine (urinary lead concentration)
suspension level: in respect of a woman of reproductive capacity, 60 µg/dl (blood-lead concentration) or 110 µg Pb/g creatinine (urinary lead concentration)



Safety Data Sheet

acc. to GB REACH

362 HMP 5C 1.2MM S

Version number: GHS 1.0

Date of compilation: 2024-11-20

Notation

Pb-med-4	medical surveillance: in respect of any other worker, 35 µg/dl (blood-lead concentration) or 40 µg Pb/g creatinine (urinary lead concentration) suspension level: in respect of a young person, 50 µg/dl (blood-lead concentration) or 110 µg Pb/g creatinine (urinary lead concentration)
wmn<45y	women of reproductive capacity (women < 45 years)
wmn>45y, men	women of non-reproductive capacity, men (women > 45 years)
young	adolescents (young person < 18 years)

8.2 Exposure controls

Appropriate engineering controls

General ventilation.

Individual protection measures (personal protective equipment)

Eye/face protection

Wear eye/face protection.

Skin protection

- Hand protection

Wear protective gloves.

- Other protection measures

Take recovery periods for skin regeneration. Preventive skin protection (barrier creams/ointments) is recommended.
Wash hands thoroughly after handling.

Respiratory protection

Particulate filter device (EN 143).

Environmental exposure controls

Use appropriate container to avoid environmental contamination. Keep away from drains, surface and ground water.

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

Physical state	solid
Colour	grey
Odour	characteristic
Melting point/freezing point	296 – 301 °C
Boiling point or initial boiling point and boiling range	>600 °C at 1,013 mbar
Flammability	non-combustible
Lower and upper explosion limit	not relevant (solid)
Flash point	not applicable
Auto-ignition temperature	>400 °C



Safety Data Sheet

acc. to GB REACH

362 HMP 5C 1.2MM S

Version number: GHS 1.0

Date of compilation: 2024-11-20

Decomposition temperature	not relevant
pH (value)	not applicable
Kinematic viscosity	not relevant
Solubility(ies)	not determined

Partition coefficient

Partition coefficient n-octanol/water (log value)	this information is not available
---	-----------------------------------

Vapour pressure	1.77 mmHg at 1,000 °C
-----------------	-----------------------

Density and/or relative density

Density	11.1 g/cm ³
Relative vapour density	not relevant (solid)

Particle characteristics	no data available
--------------------------	-------------------

9.2 Other information

Information with regard to physical hazard classes	hazard classes acc. to GHS (physical hazards): not relevant
--	--

Other safety characteristics

Liquid content	2 %
Solid content	98 %

SECTION 10: Stability and reactivity

10.1 Reactivity

Concerning incompatibility: see below "Conditions to avoid" and "Incompatible materials".

10.2 Chemical stability

See below "Conditions to avoid".

10.3 Possibility of hazardous reactions

No known hazardous reactions.

10.4 Conditions to avoid

There are no specific conditions known which have to be avoided.



Safety Data Sheet

acc. to GB REACH

362 HMP 5C 1.2MM S

Version number: GHS 1.0

Date of compilation: 2024-11-20

Hints to prevent fire or explosion

The product in the delivered form is not dust explosion capable; the enrichment of fine dust however leads to the danger of dust explosion.

10.5 Incompatible materials

There is no additional information.

10.6 Hazardous decomposition products

Reasonably anticipated hazardous decomposition products produced as a result of use, storage, spill and heating are not known. Hazardous combustion products: see section 5.

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Test data are not available for the complete mixture.

Classification procedure

The method for classification of the mixture is based on ingredients of the mixture (additivity formula).

Classification acc. to GHS

Acute toxicity

Shall not be classified as acutely toxic.

GHS of the United Nations, annex 4: May be harmful if swallowed or in contact with skin.

Skin corrosion/irritation

Shall not be classified as corrosive/irritant to skin.

Serious eye damage/eye irritation

Shall not be classified as seriously damaging to the eye or eye irritant.

Respiratory or skin sensitisation

Shall not be classified as a respiratory or skin sensitiser.

Germ cell mutagenicity

Shall not be classified as germ cell mutagenic.

Carcinogenicity

Shall not be classified as carcinogenic.

Reproductive toxicity

May damage the unborn child. May damage fertility. May cause harm to breast-fed children.

Specific target organ toxicity - single exposure

Shall not be classified as a specific target organ toxicant (single exposure).

Specific target organ toxicity - repeated exposure

Causes damage to organs through prolonged or repeated exposure.

Aspiration hazard

Shall not be classified as presenting an aspiration hazard.

11.2 Information on other hazards

There is no additional information.



Safety Data Sheet

acc. to GB REACH

362 HMP 5C 1.2MM S

Version number: GHS 1.0

Date of compilation: 2024-11-20

SECTION 12: Ecological information

12.1 Toxicity

Shall not be classified as hazardous to the aquatic environment.

12.2 Persistence and degradability

Data are not available.

12.3 Bioaccumulative potential

Data are not available.

12.4 Mobility in soil

Data are not available.

12.5 Results of PBT and vPvB assessment

According to the results of its assessment, this substance is not a PBT or a vPvB. Does not contain a PBT-/vPvB-substance at a concentration of $\geq 0,1\%$.

12.6 Endocrine disrupting properties

Does not contain an endocrine disruptor (ED) at a concentration of $\geq 0,1\%$.

12.7 Other adverse effects

Data are not available.

SECTION 13: Disposal considerations

13.1 Waste treatment methods

Sewage disposal-relevant information

Do not empty into drains. Avoid release to the environment. Refer to special instructions/safety data sheets.

Waste treatment of containers/packagegings

Completely emptied packages can be recycled. Handle contaminated packages in the same way as the substance itself.

Remarks

Please consider the relevant national or regional provisions. Waste shall be separated into the categories that can be handled separately by the local or national waste management facilities.

SECTION 14: Transport information

14.1 UN number or ID number

not subject to transport regulations

14.2 UN proper shipping name

not relevant

14.3 Transport hazard class(es)

none

14.4 Packing group

not assigned

14.5 Environmental hazards

non-environmentally hazardous acc. to the dangerous goods regulations

14.6 Special precautions for user

There is no additional information.



Safety Data Sheet

acc. to GB REACH

362 HMP 5C 1.2MM S

Version number: GHS 1.0

Date of compilation: 2024-11-20

14.7 Maritime transport in bulk according to IMO instruments

The cargo is not intended to be carried in bulk.

Information for each of the UN Model Regulations

International Maritime Dangerous Goods Code (IMDG) - Additional information

Not subject to IMDG.

International Civil Aviation Organization (ICAO-IATA/DGR) - Additional information

Not subject to ICAO-IATA.

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

Relevant provisions of the European Union (EU)

Deco-Paint Directive

VOC content	0.03814 %
-------------	-----------

Industrial Emissions Directive (IED)

VOC content	0.03814 %
-------------	-----------

Directive on the restriction of the use of certain hazardous substances in electrical and electronic equipment (RoHS)

Hazardous substances in electrical and electronic equipment (RoHS)	
Name acc. to inventory	Maximum concentration values tolerated by weight in homogeneous materials
lead	0,1 % Pb

Regulation concerning the establishment of a European Pollutant Release and Transfer Register (PRTR)

Pollutant release and transfer registers (PRTR)			
Name of substance	CAS No	Remarks	Threshold for releases to air (kg/year)
Lead	7439-92-1	(8)	200

Legend

(8) All metals shall be reported as the total mass of the element in all chemical forms present in the release



Safety Data Sheet

acc. to GB REACH

362 HMP 5C 1.2MM S

Version number: GHS 1.0

Date of compilation: 2024-11-20

Water Framework Directive (WFD)

List of pollutants (WFD)			
Name of substance	CAS No	Listed in	Remarks
Silver		a)	
Lead	7439-92-1	b)	
Lead		b)	
Lead		c)	
Lead		a)	
Lead		a)	

Legend

- a) Indicative list of the main pollutants
- b) List of priority substances in the field of water policy
- c) Environmental Quality Standards for Priority Substances and certain other pollutants

Regulation concerning the export and import of hazardous chemicals (PIC)

Chemicals subject to the international prior informed consent (PIC) procedure (the 'PIC procedure').

Name of substance	CAS No	Category / subcategory	Use limitation
Lead		i(2)	sr

Legend

- i(2) Sub-category: i(2) - industrial chemical for public use
- sr Use limitation: severe restriction (for the sub-category or sub-categories concerned) according to Union legislation

Regulation on persistent organic pollutants (POP)

none of the ingredients are listed

National regulations (GB)

List of substances subject to authorisation (GB REACH, Annex 14) / SVHC - candidate list

Substance of Very High Concern (SVHC) acc. to GB REACH and HSE			
Name of substance	CAS No	Listed in	Remarks
Lead	7439-92-1	Candidate list	Repr. A57c

Legend

- Candidate list Substances meeting the criteria referred to in Article 57 and for eventual inclusion in Annex XIV
- Repr. A57c Toxic for reproduction (Article 57c)



Safety Data Sheet

acc. to GB REACH

362 HMP 5C 1.2MM S

Version number: GHS 1.0

Date of compilation: 2024-11-20

Restrictions according to GB REACH, Annex 17

Dangerous substances with restrictions (GB REACH, Annex 17)			
Name of substance	Name acc. to inventory	CAS No	No
Lead	toxic for reproduction		30
Lead	Lead compounds		63
Lead	Lead compounds		72

15.2 Chemical safety assessment

Chemical safety assessments for substances in this mixture were not carried out.

SECTION 16: Other information

Abbreviations and acronyms

Abbr.	Descriptions of used abbreviations
ADR	Accord relatif au transport international des marchandises dangereuses par route (Agreement concerning the International Carriage of Dangerous Goods by Road)
Aquatic Acute	Hazardous to the aquatic environment - acute hazard
Aquatic Chronic	Hazardous to the aquatic environment - chronic hazard
ATE	Acute Toxicity Estimate
CAS	Chemical Abstracts Service (service that maintains the most comprehensive list of chemical substances)
Ceiling-C	Ceiling value
CLWR	Control of Lead at Work Regulations
DGR	Dangerous Goods Regulations (see IATA/DGR)
EC No	The EC Inventory (EINECS, ELINCS and the NLP-list) is the source for the seven-digit EC number, an identifier of substances commercially available within the EU (European Union)
ED	Endocrine disruptor
EH40/2005	EH40/2005 Workplace exposure limits (http://www.nationalarchives.gov.uk/doc/open-government-licence/)
EINECS	European Inventory of Existing Commercial Chemical Substances
ELINCS	European List of Notified Chemical Substances
GB REACH	The REACH etc. (Amendment etc.) (EU Exit) Regulations 2019, SI 2019/758 (as amended)
GHS	"Globally Harmonized System of Classification and Labelling of Chemicals" developed by the United Nations
HSE	Health and Safety Executive
IATA	International Air Transport Association
IATA/DGR	Dangerous Goods Regulations (DGR) for the air transport (IATA)
ICAO	International Civil Aviation Organization
IMDG	International Maritime Dangerous Goods Code



Safety Data Sheet

acc. to GB REACH

362 HMP 5C 1.2MM S

Version number: GHS 1.0

Date of compilation: 2024-11-20

Abbr.	Descriptions of used abbreviations
index No	The Index number is the identification code given to the substance in Part 3 of Annex VI to Regulation (EC) No 1272/2008
Lact.	Effects on or via lactation
M-factor	Means a multiplying factor. It is applied to the concentration of a substance classified as hazardous to the aquatic environment acute category 1 or chronic category 1, and is used to derive by the summation method the classification of a mixture in which the substance is present
NLP	No-Longer Polymer
OEL	Workplace exposure limit
PBT	Persistent, Bioaccumulative and Toxic
ppm	Parts per million
Repr.	Reproductive toxicity
RID	Règlement concernant le transport International ferroviaire des marchandises Dangereuses (Regulations concerning the International carriage of Dangerous goods by Rail)
STEL	Short-term exposure limit
STOT RE	Specific target organ toxicity - repeated exposure
TWA	Time-weighted average
VOC	Volatile Organic Compounds
vPvB	Very Persistent and very Bioaccumulative
WEL	Workplace exposure limit

Key literature references and sources for data

Agreement concerning the International Carriage of Dangerous Goods by Road (ADR). Regulations concerning the International Carriage of Dangerous Goods by Rail (RID). International Maritime Dangerous Goods Code (IMDG). Dangerous Goods Regulations (DGR) for the air transport (IATA).

Classification procedure

Physical and chemical properties: The classification is based on tested mixture.

Health hazards, Environmental hazards: The method for classification of the mixture is based on ingredients of the mixture (additivity formula).

List of relevant phrases (code and full text as stated in section 2 and 3)

Code	Text
H360FD	May damage fertility. May damage the unborn child.
H362	May cause harm to breast-fed children.
H372	Causes damage to organs through prolonged or repeated exposure.
H400	Very toxic to aquatic life.
H410	Very toxic to aquatic life with long lasting effects.

Disclaimer

This information is based upon the present state of our knowledge. This SDS has been compiled and is solely intended for this product.