




used for: D-SUB DUAL-PORT

No. of pos.	A	B	C	Part-N0.
2x 9	16.92	25.00	30.80	DLS1PP5AN21X
2x15	25.25	33.30	39.20	DLS2PP5AN21X
2x25	38.96	47.10	53.10	DLS3PP5AN21X
2x37	55.42	63.50	69.40	DLS4PP5AN21X



(b) SPECIFICATION:

1. MATERIAL:

INSULATOR: THERMAL PLASTIC UL 94 V-0

CONTACTS: COPPER ALLOY

SHELL: STEEL

RIVET, BOARDLOCK: COPPER ALLOY

2. CONTACT PLATING:

UNDERPLATE: 50µin NICKEL

CONTACT AREA: GOLD FLASH

SOLDER TAILS AREA: GOLD FLASH

3. ELECTRICAL:

OPERATION VOLTAGE: 250 VAC max.

CURRENT RATING: 3 A max.


CONTACT RESISTANCE: 25 mOhm max.

INSULATION RESISTANCE: 3000 MOhm min. @ 500 VDC

DIELECTRIC WITHSTANDING VOLTAGE: 1000 VAC / MINUTE

OPERATING TEMPERATURE: -55°C TO +105°C

4. CONNECTOR IS PART MARKED: [PART-NO. CONEC ABC]

RECOMMENDED P.C.B. LAYOUT (TOP VIEW)
TOLERANCES: ±0.1mm

APPROVAL * FREIGABE * DEBLOCKAGE * AUTOR/ZACON * APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL * FREIGABE * DEBLOCKAGE * AUTOR/ZACON * APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY, WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

6 x b	Ä3285	10.02.2009	Sonne
a	Origin		
rev.	description	date	name

tolerance	ANG.	±5°
(b)	0	±0.5
	0	±0.3
	00	±0.2
dim. in mm		
date	name	
2003	Parei	
drawn	26.03.	Kühle
appd.	26.03.	
norm		
d-old		

scale:	2:1
material:	SEE NOTES
title:	D-SUB DUAL-PORT MALE / MALE 2x9pos. - 2x37pos. with 4-40 insert
dwg no:	AutoCAD 2000
part no:	SEE TABLE
DIN-A	3
sh:	1/1

CONEC®