XUB9BPXWM12

Photoelectric sensors XU, photo electric sensor, cylindrical, metal, angled, polarised, Smax 5.5 m, PNP, Connector M12



Main

Range of product	Telemecanique Photoelectric sensors XU	
Series name	General purpose single mode	
Electronic sensor type	Photo-electric sensor	
Sensor name	XUB	
Sensor design	Cylindrical M18	
Detection system	Polarised reflex	
Material	Metal	
Line of sight type	90° lateral	
Type of output signal	Discrete	
Supply circuit type	DC	
Wiring technique	4 wires	
Discrete output type	PNP	
Discrete output function	1 NO or 1 NC programmable	
Electrical connection	1 male connector M12, 4 pins	
Emission	Red LED polarised reflex	
[Sn] nominal sensing distance	4 m polarised reflex need reflector XUZC50	

Complementary

Complementary		
Enclosure material	PC/PBT	
Lens material	PMMA	
Maximum sensing distance	5.5 m polarised reflex	
Output type	Discrete	
Status LED	1 LED (green) for supply on/stability 1 LED (orange) for output state	
[Us] rated supply voltage	1224 V DC with reverse polarity protection	
Supply voltage limits	1030 V DC	
Switching capacity in mA	<= 100 mA (overload and short-circuit protection)	
Switching frequency	<= 1000 Hz	
Maximum voltage drop	<2 V (closed state)no-load	
Current consumption	< 20 mA no load	
Maximum delay first up	100 ms	
Maximum delay response	0.5 ms	
Maximum delay recovery	0.5 ms	
Setting-up	Sensitivity by potentiometer	
Diameter	18 mm	
Length	55.2 mm	
Net weight	0.060 kg	

Environment

Product certifications	CE[RETURN]cULus[RETURN]UKCA[RETURN]RoHS	
Ambient air temperature for operation	-3055 °C	
Ambient air temperature for storage	-4070 °C	
Relative humidity	3595 %	
Immunity to ambient light	40000 Lux sunlight 10000 lux incandescent light	

Vibration resistance	7 gn, amplitude = +/- 1.5 mm (f = 1055 Hz)for every axis conforming to IEC 60068-2-6	
Shock resistance	30 gn (duration = 11 ms) for for every axis conforming to IEC 60068-2-27	
IP degree of protection	IP67 conforming to IEC 60529 IP65 conforming to IEC 60529 IP69K conforming to DIN 40050-9	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.8 cm
Package 1 Width	1.6 cm
Package 1 Length	4.4 cm
Package 1 Weight	40 g
Unit Type of Package 2	S02
Number of Units in Package 2	48
Package 2 Height	15 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	2.235 kg
Unit Type of Package 3	P06
Number of Units in Package 3	768
Package 3 Height	70 cm
Package 3 Width	60 cm
Package 3 Length	80 cm
Package 3 Weight	44.26 kg

Contractual warranty

Warranty	18 months	

