XUT9ALPXP02

Photoelectric sensors XUT9, Reflex, Laser, Sn 3000mm, IO-Link, Pigtail M8 20cm



Main

Range of product	Telemecanique Photoelectric sensors XU
Series name	Application packaging
Electronic sensor type	Photo-electric sensor
Sensor name	XUT
Sensor design	Sub-miniature
Detection system	Polarised reflex
Material	Plastic
Type of output signal	Discrete
Supply circuit type	DC
Discrete output type	PNP/NPN autodetect IOLINK
Discrete output function	1 NO or 1 NC programmable
Electrical connection	1 male connector M8, 4 pins
Cable length	0.2 m
Product specific application	Reflex laser
Emission	Red laser reflex
[Sn] nominal sensing distance	3 m reflex

Complementary

Complementary	
Enclosure material	PUR
Lens material	PMMA
Maximum sensing distance	4 m reflex
Output type	Solid state
Output function governance	NO/NC programmable
Add on output	Without, 50 mA
Add on input	Remote teaching
Wire insulation material	PVC
Status LED	1 LED (green) for power ON
[Us] rated supply voltage	1224 V DC with reverse polarity protection
Supply voltage limits	1030 V DC
Switching capacity in mA	<= 50 mA (overload and short-circuit protection)
Switching frequency	<= 1000 Hz
Current consumption	<= 12 mA no-load
Maximum delay first up	300 ms
Maximum delay response	500 µs
Maximum delay recovery	300 ms
Setting-up	Sensitivity adjustment with teach mode
Height	21.1 mm
Length	14.6 mm
Width	8 mm
Net weight	0.02 kg

Environment

Product certifications	CE
Ambient air temperature for operation	-2060 °C
Ambient air temperature for storage	-2080 °C
IP degree of protection	IP67 conforming to IEC 60529

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.1 cm
Package 1 Width	3.1 cm
Package 1 Length	6.1 cm
Package 1 Weight	28 g
Unit Type of Package 2	S01
Number of Units in Package 2	30
Package 2 Height	15 cm
Package 2 Width	15 cm
Package 2 Length	40 cm
Package 2 Weight	1.075 kg

Contractual warranty

To monate		18 months	
-----------	--	-----------	--