











2 CONTACTS WILL BE SUPPLIED LOOSE

STRIPPING DIMENSIONS



NOTES:

1. MATERIAL AND FINISH:

- PLUG HOUSING: PA (BLACK); UL94 V-0; UL (f1) RATED
- PANEL NUT: BRASS; FINISH: NICKEL PLATED
- PANEL GASKET: SILICONE; COLOR: WHITE

2. HIGH POWER CONTACTS; CRIMP; 30A

- FOR USE WITH CABLE AWG 8* - 10
- MATERIAL: COPPER ALLOY
- PLATING, MATING AREA: GOLD FLASH over NICKEL
- PLATING, TERMINATION SIDE: 160-240µin TIN over 80µin NICKEL
- CONTACTS WILL BE SUPPLIED LOOSE
- CRIMPING: USE CRIMP TOOL 360X10409X

WITH TOOL INSERT 360X20029X

SELECTOR SETTINGS: 5 FOR AWG 8*; 4 FOR AWG 10

3. OPERATING TEMPERATURE: -40°C to +100°C

4. WORKING VOLTAGE: 48V AC/DC

5. CONNECTOR CAN BE FRONT MOUNTED TO A MAXIMUM PANEL THICKNESS OF 5,9mm

6. IP67 RATED WHEN COVERED OR FULLY MATED WITH THE APPROPRIATE MATING CONNECTOR

7. *NOTE: FOR AWG 8 STRANDED 19/21, 37/24 and 65/26 WIRE ONLY

RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND				 dim. in mm		scale: 2:1			
						material: SEE NOTES			
								title: IP67 POWER BAYONET 2pos. PLUG KIT / CRIMP panel mount	
						date	name		
						drawn 27.10.2015	Lehmenkühler		
		appd. 27.10.2015	Koch	dwg no: 17K1A474		DIN- A3 sh: 1			
		norm							
		d-old							
1 x b	Ä21-0426	05.11.2021	Bub						
a	Original								
rev.	description	date	name	part no: 17-400503					