

DTM04-2P-EP10

✓ ACTIVE

DEUTSCH | DEUTSCH DT, DEUTSCH DTM

TE Internal #: DTM04-2P-EP10

2 Position Housing, Housing for Male Terminals, Component-to-Wire, 4.19 mm [.165 in] Centerline, Sealable, Black, Wire & Cable, Power, Hybrid

[View on TE.com >](#)



Connectors > Automotive Connectors > Automotive Housings > DEUTSCH DTM Housings



Number of Positions: 2

Connector & Housing Type: **Housing for Male Terminals**

Mating Pin Diameter: 1.02 mm [.04 in]

Connector System: **Component-to-Wire**

Centerline (Pitch): 4.19 mm [.165 in]

[All DEUTSCH DTM Housings \(113\)](#)

Features

Industry Standards

IP Rating	IP6K9K, IP68
Compatible With Agency/Standards Products	SAE J2030
UL Flammability Rating	20mm Flame Test per Standard UL-94

Mechanical Attachment

Strain Relief	Add By Accessory
Terminal Position Assurance	Yes
Mating Alignment Type	Keyed
Mating Alignment	With

Dimensions

Compatible Insulation Diameter Range	1.35 – 3.05 mm[.053 – .12 in]
Product Width	16.54 mm[.651 in]
Product Length	42.67 mm[1.68 in]



Connector Height	16.21 mm[.638 in]
Packaging Features	
Packaging Quantity	1000
Packaging Method	Box
Other	
Serviceable	No
Connector Position Assurance Capable	No
EU RoHS Compliance	Compliant with Exemptions
EU ELV Compliance	Compliant with Exemptions
Electrical Characteristics	
Operating Voltage	250 VDC
Nominal Voltage Architecture	250 V
Body Features	
Cable Exit Angle	180°
Primary Product Color	Black
Connector & Keying Code	B
Housing Features	
Housing Material	PA GF
Centerline (Pitch)	4.19 mm[.165 in]
Contact Features	
Contact Size	Size 20
Contact Type	Pin
Mating Pin Diameter	1.02 mm[.04 in]
Contact Current Rating (Max)	7.5 A
Product Type Features	
Mixed & Hybrid Connector	No
Connector Shape	Rectangular
Connector & Housing Type	Housing for Male Terminals
Connector System	Component-to-Wire
Sealable	Yes
Primary Locking Feature	Integrated in Housing
Connector & Contact Terminates To	Wire & Cable



Configuration Features

Blank Cavity Position	0
Connector Modification	Terminating Resistor, J1939
Number of Positions	2
Number of Rows	1

Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]

Operation/Application

Circuit Application	Power
---------------------	-------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2023 (235) SVHC > Threshold: Pb (1.2% in component part) Octamethylcyclotetrasiloxane (D4) (.5% in component part) Decamethylcyclopentasiloxane (D5) (.5% in component part) Dodecamethylcyclohexasiloxane (D6) (.5% in component part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part



numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

Also in the Series | DEUTSCH DT



Connector Strain Relief(28)




Insertion & Extraction Tools(2)



Other Automotive Connector Accessories(7)




Rectangular Backshells & Clamps(1)



Wire-to-Board Headers & Receptacles (38)


Also in the Series | **DEUTSCH DTM**



Automotive Connector Locks & Position Assurance(26)



Automotive Headers(38)



Automotive Housings(109)




Connector Strain Relief(28)



Insertion & Extraction Tools(2)




Other Automotive Connector Accessories(7)



PCB Headers & Receptacles(38)



Rectangular Backshells & Clamps(1)



Wire-to-Board Headers & Receptacles (38)



Customers Also Bought

TE Part #2342926-1
4POS,MCON 1.2,TAB HSG ASSY,SLD

TE Part #2430382-2
RING TONGUE TRMNL,IPT RING TONGUE 150MM2

TE Part #DTM06-2S
PLG, 2P, GRY, N

TE Part #DT16-6SA-KP01
PLG, 6P, GRY, E, A

TE Part #2407799-1
COVER,SHIPPING CAP FOR HD1400 PLUG

TE Part #2-1703820-1
6POS,TAB 1.6X0.6,TAB HSG,ASSY

TE Part #9-1768017-2
EET-0820P-4

TE Part #521217-2
ULTRA-POD 250 ASSY TAB 18-14 AWG TPBR

TE Part #61867-2
RING CRIMP 18-14 AWG TPBR

TE Part #6-1355512-7
47 WAY ABS CONNECTOR

Documents

Product Drawings

REC, 2P, BLK, 120 OHM RESISTOR, AU, B

English

CAD Files

Customer View Model

ENG_CVM_CVM_DTM04-2P-EP10_99.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_DTM04-2P-EP10_99.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_DTM04-2P-EP10_99.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



Datasheets & Catalog Pages

TERMINALS AND CONNECTORS

English

ICT Terminals and Connectors Catalogue

English

CONNECTOR SELECTOR

English

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English