

HDP26-24-35SE

✓ ACTIVE

DEUTSCH | DEUTSCH HDP, DEUTSCH HD

TE Internal #: HDP26-24-35SE

35 Position Housing, Housing for Female Terminals, Wire-to-Panel, Sealable, Black, Wire & Cable, Power, Panel Mount, Hybrid

[View on TE.com >](#)



Connectors > Automotive Connectors > Automotive Housings > DEUTSCH HDP20 Housings



Number of Positions: 35

Connector & Housing Type: Housing for Female Terminals

Mating Pin Diameter: 1.6 mm, 1 mm [.063 in, .04 in]

Connector System: Wire-to-Panel

Sealable: Yes

[All DEUTSCH HDP20 Housings \(357\)](#)

Features

Housing Features

Housing Material	PA 66 GF
------------------	----------

Industry Standards

IP Rating	IP67
UL Flammability Rating	UL 94V-0

Dimensions

Compatible Insulation Diameter Range	1.9 – 3.2 mm, 1.4 – 3.8 mm[.055 – .15 in][.075 – .125 in]
Product Width	49.5 mm[1.95 in]
Product Length	49.5 mm[1.95 in]
Connector Height	38.6 mm[1.52 in]

Packaging Features

Packaging Quantity	40
Packaging Method	Tray



Mechanical Attachment

Strain Relief	Without
Terminal Position Assurance	No
Mating Alignment Type	Polarizing Slot
Mating Alignment	With
Connector Mounting Type	Panel Mount

Other

Serviceable	Yes
Connector Position Assurance Capable	No
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Electrical Characteristics

Operating Voltage	250 VDC
Nominal Voltage Architecture	250 V

Body Features

Cable Exit Angle	180°
Primary Product Color	Black

Contact Features

Contact Size	Size 16, Size 20
Contact Type	Socket
Mating Pin Diameter	1.6 mm, 1 mm[.063 in][.04 in]
Contact Current Rating (Max)	13 A, 7.5 A

Product Type Features

Mixed & Hybrid Connector	Yes
Connector Shape	Circular
Connector & Housing Type	Housing for Female Terminals
Connector System	Wire-to-Panel
Sealable	Yes
Primary Locking Feature	Contact Retainer
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Blank Cavity Position	0
-----------------------	---



Connector Seal Code	E Seal
Number of Positions	35

Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]

Operation/Application

Circuit Application	Power
---------------------	-------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2023 (233) SVHC > Threshold: Octamethylcyclotetrasiloxane (D4) (.4% in Component part) Article Safe Usage Statements: Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # 0411-240-2005
EXT TOOL, SIZE 20, 16-22 AWG, N, RED



TE Part # HD30-24BT
BOOT, 24SZ, ST, GRY



TE Part # HD30-24BT-90-BK
BOOT, 24SZ, RA, BLK



TE Part # CAT-D48-SP729
DEUTSCH Sealing Plugs



TE Part # 0411-336-1605
EXT TOOL, SIZE 16, 16-20 AWG, E, DRK BLU




TE Part # CAT-H396-CH8172
DEUTSCH HDP20 Housings




TE Part # HD30-24BT-BK
BOOT, 24SZ, ST, BLK


Also in the Series | **DEUTSCH HD**



Automotive Headers(1)



Automotive Housings(357)



Connector Backshells(10)



Connector Strain Relief(5)



Insertion & Extraction Tools(11)



Other Automotive Connector Accessories(6)



PCB Headers & Receptacles(1)



Wire-to-Board Headers & Receptacles (1)

Also in the Series | **DEUTSCH HDP**




Automotive Connector Caps & Covers (4)



Automotive Housings(357)



Insertion & Extraction Tools(11)



Other Automotive Connector Accessories(6)

Customers Also Bought



TE Part #CAT-M8793-CH8172
MQS, CONNECTOR HOUSING



TE Part #2320281-1
PICO MQS,TERMINAL



TE Part #DTM06-4S-E004
PLG, 4P, BLK, N



TE Part #CAT-N54-PPRHU222
PicoMQS, 2-22 POS REC HSG, Unsealed



TE Part #8-34113-1
SOLIS R 22-16COMM 22-18MIL1/4



TE Part #1060-20-0177
PIN, SF, SIZE 20, 16-22, SN/SN



TE Part #8-34151-1
PG R 22-16 COMM 22-18 MIL 5/16



TE Part #3-31173-3
BUDG R 22-16COMM 22-18MIL 5/16

Documents

Product Drawings

PLG, 35P, BLK, E, 16/20, S

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_HDP26-24-35SE_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_HDP26-24-35SE_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_HDP26-24-35SE_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.



Datasheets & Catalog Pages

DEUTSCH HD30 & HDP20 CONNECTOR SERIES

English

CONNECTOR SELECTOR

English

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English