



Pushing Performance
Since 1945

Han M12 Crimp X-coded female



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 881 2805
Specification	Han M12 Crimp X-coded female
HARTING eCatalogue	https://b2b.harting.com/09148812805

Identification

Category	Inserts
Series	Han-Modular®

Version

Termination method	Crimp termination
Gender	Female
Number of contacts	8
further contacts	+ shielding
Coding	X-coding
Details	Please order crimp contacts separately.

Technical characteristics

Conductor cross-section	0.08 ... 0.25 mm²
Conductor cross-section [AWG]	AWG 28 ... AWG 23
Wire outer diameter	≤1.4 mm
Rated current	0.5 A
Rated voltage	32 V
Rated impulse voltage	0.8 kV
Pollution degree	3
Transmission characteristics	Cat. 6 _A Class E _A up to 500 MHz



Pushing Performance
Since 1945

Technical characteristics

Data rate	10 Mbit/s
	100 Mbit/s
	1 Gbit/s
	2.5 Gbit/s
	5 Gbit/s
	10 Gbit/s
Insulation resistance	$>10^8 \Omega$
Contact resistance	$\leq 10 \text{ m}\Omega$
Contact resistance, shielding	$\leq 100 \text{ m}\Omega$
Tightening torque	0.6 Nm
Wrench size	12
	13
Limiting temperature	-40 ... +85 °C
Mating cycles	≥ 500
Cable diameter	5.5 ... 8.7 mm

Material properties

Material (insert)	Liquid crystal polymer (LCP)
Material (shielding)	Copper alloy, nickel plated
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3)
	R23 (HL 1-3)

Specifications and approvals

Specifications	IEC 60664-1
	IEC 61984

Commercial data

Packaging size	1
----------------	---



Pushing Performance
Since 1945

Commercial data

Net weight	30 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140187825
ETIM	EC000438
eCl@ss	27440205 Contact insert for industrial connectors