

[Calculator](#)[LMR® Cables](#)[Products](#)[Markets & Applications](#)[Resources](#)

EZ-600-FM-75-X

Type F, male (plug), straight, EZ style connector for LMR®-600-75 type cables. The EZ-600-FM-75-X eliminates assembly errors and soldering with crimp-style outer contacts and spring finger inner contacts. It features a no-braid trim design, eliminating FOD and guaranteeing an optimal and consistent termination. The BeCu pins are designed to maximize surface contact and minimize current density. They provide a strong spring force making the EZ connectors a perfect choice for extreme cold and high-vibration applications where the

Inventory Status

Distributor		Qty
Mouser Electronics		61



Showing 1 to 1 of 1 entries



1



center conductor might contract. The F-Type connector series is a durable, high-performance threaded interface originally designed for cable television (CATV), set top boxes and cable modems. It is often used with 75Ohm cable options.



Stock Code: **3190-6410**

F Male (plug)

**1**

Specs	Compatible with	Hardware	CAD Model
	Documentation	Ask an Expert	

Specifications

Part Number	EZ-600-FM-75-X	Max Frequency (GHz)	1	Pin Finish	Gold
Stock Code	3190-6410	VSWR Freq	<1.30:1	Length (mm)	51.4
Interface	F	VSWR Frequency (GHz)	1	Length (in)	2.02
Gender	male (plug)	Coupling Nut	Hex	Width (mm)	17.5
Orientation	Straight	Inner Contact Attach	Spring Finger	Width (in)	0.69
				Weight (g)	12.64

PIM Rating		Outer Contact Attach	Crimp	Weight (lb)	0.03
Impedance (ohms)	75	Body Finish	Alballoy		

Compatible with

LMR-600-75

LMR-600-75-DB

LMR-600-75-FR


Tools and Accessories



Grounding Kits



Cold Shrink Weatherproofing



Hoisting G

Documentation

EZ-600-FM-75-X Connector Drawing

Download

EZ-600-FM-75-X Installation
Instructions

Download

EZ-600-FM

Dow

Subscribe to our newsletter!

Interested in receiving email newsletters and other updates from Times? Subscribe now!

First name*

Last name*

Company

Email*

Subscribe



Products

Cables and
Assemblies
Connectors

Quick Links

Markets
Applications
Resources

Markets

Space
Land, Mobile,
Radio and

Contact Us

Test and
Measurement
Products
Tools
Accessories

About Us
Careers
News
Privacy Policy


Public Network
Unmanned
Aerial Vehicles
Quantum
Computing
Test and
Measurement

Follow Us




First name* Last name*

Country *

Please Select 

Email*

Message



protected by reCAPTCHA

[Privacy](#) - [Terms](#)

Submit

Times Microwave Systems,
358 Hall Avenue, Wallingford,
CT 06492, USA
T: +1 (800) 867-2629
F: 203-949-8423

Times Microwave Systems,
Shanghai, China
T: 86-21-51761234
F: 021-64424098

Times Microwave Systems,
No. 65, 2nd Floor, MGM Magnum,
Electronic City Phase 1, Bengaluru-
560100

T: (080) 6861-1611

Copyright © 2024 Times Microwave Systems. All Rights Reserved. InstaBend[®], LLPL[®], LLPX[®], LLSB[®], LMR[®], LMR-lite[®], M8[®], M8M[®], MaxGain[®], Miltech[®], nu-Trac[®], PhaseTrack[®], Smart-Panel[®], Stripflex[®], T-COM[®], Testmate[®], TF4[®], T-Flex[®], Times Microwave Systems[®], TIMES PROTECT and Design[®], Times-Protect[®], T-Rad[®], TuffGrip[®], Xtended Flex[®] are Registered Trademarks of Times Microwave Systems.