

Revision date 12/07/2023

Revision Number 1.81

SECTION 1: Identification of the substance/mixture and of the company/undertaking**1.1. Product identifier**

Product Name Silicone Heat Transfer Compound

Product Code(s) HTS, EHTS05G, EHTS10S, EHTS35SL, EHTS700GS, EHTS01K, EHTS25K, ZE

Safety data sheet number 00507

Pure substance/mixture Mixture

1.2. Relevant identified uses of the substance or mixture and uses advised against

Recommended use Heat Dissipation

Uses advised against No specific uses advised against are identified

1.3. Details of the supplier of the safety data sheet

Manufacturer	Supplier
ELECTROLUBE MacDermid Alpha Electronics Solutions ASHBY PARK, COALFIELD WAY, ASHBY DE LA ZOUCH, LEICESTERSHIRE LE65 1JR UNITED KINGDOM	HK WENTWORTH LIMITED 32 RUE DE TOURNENFILS 91540 MENNECY FRANCE
+44 (0)1530 419600 +44 (0)1530 416640 info@electrolube.com	+33 (0) 1 82 88 47 94 info@electrolube.com

For further information, please contact

E-mail address info@electrolube.com

1.4. Emergency telephone number

Emergency Telephone POISON INFORMATION CENTRE (Beaumont Hospital, Republic of Ireland only) +353 (0)1 809 2166 (08:00 - 22:00)

Emergency Telephone - IN CASE OF EMERGENCY CALL: +44 1865 407333 (24hr, Provided by Carechem 24)**SECTION 2: Hazards identification****2.1. Classification of the substance or mixture**

Regulation (EC) No 1272/2008

Acute aquatic toxicity	Category 1 - (H400)
-------------------------------	---------------------

Chronic aquatic toxicity

Category 1 - (H410)

2.2. Label elements



Signal word

Warning

Hazard statements

H410 - Very toxic to aquatic life with long lasting effects

Precautionary Statements - EU (§28, 1272/2008)

P273 - Avoid release to the environment.

P391 - Collect spillage.

P501 - Dispose of contents/container in accordance with local, regional, national, and international regulations as applicable.

2.3. Other hazards

This mixture contains no substance considered to be persistent, bioaccumulating or toxic (PBT). This mixture contains no substance considered to be very persistent nor very bioaccumulating (vPvB).

Endocrine Disruptor Information This product does not contain any known or suspected endocrine disruptors.

SECTION 3: Composition/information on ingredients

3.1 Substances

Not applicable

3.2 Mixtures

Chemical name	Weight-%	REACH registration number	EC No (EU Index No)	Classification according to Regulation (EC) No. 1272/2008 [CLP]	Specific concentration limit (SCL)	M-Factor	M-Factor (long-term)
zinc oxide 1314-13-2	60-100	01-2119463881-32-00 00	215-222-5	Aquatic Chronic 1 (H410) Aquatic Acute 1 (H400)	-	-	-

Full text of H- and EUH-phrases: see section 16

Acute Toxicity Estimate

If LD50/LC50 data is not available or does not correspond to the classification category, then the appropriate conversion value from CLP Annex I, Table 3.1.2, is used to calculate the acute toxicity estimate (ATEmix) for classifying a mixture based on its components

Chemical name	Oral LD50 mg/kg	Dermal LD50 mg/kg	Inhalation LC50 - 4 hour - dust/mist - mg/L	Inhalation LC50 - 4 hour - vapour - mg/L	Inhalation LC50 - 4 hour - gas - ppm
zinc oxide 1314-13-2	5000	2000	5.7	No data available	No data available

This product does not contain candidate substances of very high concern at a concentration $\geq 0.1\%$ (Regulation (EC) No. 1907/2006 (REACH), Article 59)

SECTION 4: First aid measures

4.1. Description of first aid measures

General advice	Show this safety data sheet to the doctor in attendance.
Inhalation	Remove to fresh air.
Eye contact	Rinse thoroughly with plenty of water for at least 15 minutes, lifting lower and upper eyelids. Consult a doctor.
Skin contact	Wash off immediately with plenty of water for at least 15 minutes. If symptoms persist, call a doctor.
Ingestion	Do NOT induce vomiting. Rinse mouth. Never give anything by mouth to an unconscious person. Call a doctor.
Self-protection of the first aider	Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination. Wear personal protective clothing (see section 8).

4.2. Most important symptoms and effects, both acute and delayed

Symptoms	No information available.
Effects of Exposure	No information available.

4.3. Indication of any immediate medical attention and special treatment needed

Note to doctors	Treat symptomatically.
------------------------	------------------------

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable Extinguishing Media	Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
Large Fire	CAUTION: Use of water spray when fighting fire may be inefficient.
Unsuitable extinguishing media	Do not scatter spilled material with high pressure water streams.

5.2. Special hazards arising from the substance or mixture

Specific hazards arising from the chemical	No information available.
---	---------------------------

5.3. Advice for firefighters

Special protective equipment and precautions for fire-fighters	Firefighters should wear self-contained breathing apparatus and full firefighting turnout gear. Use personal protection equipment.
---	--

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions	Avoid contact with skin, eyes or clothing. Ensure adequate ventilation. Use personal protective equipment as required.
Other information	Refer to protective measures listed in Sections 7 and 8.
For emergency responders	Use personal protection recommended in Section 8.

6.2. Environmental precautions

Environmental precautions	Prevent further leakage or spillage if safe to do so.
----------------------------------	---

6.3. Methods and material for containment and cleaning up

Methods for containment	Prevent further leakage or spillage if safe to do so.
Methods for cleaning up	Take up mechanically, placing in appropriate containers for disposal.
Prevention of secondary hazards	Clean contaminated objects and areas thoroughly observing environmental regulations.

6.4. Reference to other sections

Reference to other sections	See section 8 for more information. See section 13 for more information.
------------------------------------	--

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Advice on safe handling	Handle in accordance with good industrial hygiene and safety practice. Avoid contact with skin, eyes or clothing. Ensure adequate ventilation.
General hygiene considerations	Avoid contact with skin, eyes or clothing. Wear suitable gloves and eye/face protection.

7.2. Conditions for safe storage, including any incompatibilities

Storage Conditions	Keep containers tightly closed in a dry, cool and well-ventilated place. Store locked up.
Storage class (TRGS 510)	LGK 10.

7.3. Specific end use(s)

Risk Management Methods (RMM)	The information required is contained in this Safety Data Sheet.
--------------------------------------	--

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Exposure Limits

Chemical name	European Union	Austria	Belgium	Bulgaria	Croatia
zinc oxide 1314-13-2	-	TWA: 5 mg/m ³	TWA: 2 mg/m ³ STEL: 10 mg/m ³	STEL: 10.0 mg/m ³ TWA: 5.0 mg/m ³	TWA: 2 mg/m ³ STEL: 10 mg/m ³
Chemical name	Cyprus	Czech Republic	Denmark	Estonia	Finland
zinc oxide 1314-13-2	-	TWA: 2 mg/m ³ Ceiling: 5 mg/m ³	TWA: 4 mg/m ³ STEL: 8 mg/m ³	TWA: 5 mg/m ³	TWA: 2 mg/m ³ STEL: 10 mg/m ³
Chemical name	France	Germany TRGS	Germany DFG	Greece	Hungary
zinc oxide 1314-13-2	TWA: 5 mg/m ³ TWA: 10 mg/m ³	-	TWA: 0.1 mg/m ³ TWA: 2 mg/m ³ Peak: 0.4 mg/m ³ Peak: 4 mg/m ³	TWA: 5 mg/m ³ STEL: 10 mg/m ³	TWA: 5 mg/m ³
Chemical name	Ireland	Italy MDLPS	Italy AIDII	Latvia	Lithuania
zinc oxide 1314-13-2	TWA: 2 mg/m ³ STEL: 10 mg/m ³	-	TWA: 2 mg/m ³ STEL: 10 mg/m ³	TWA: 0.5 mg/m ³	TWA: 5 mg/m ³
Chemical name	Luxembourg	Malta	Netherlands	Norway	Poland
zinc oxide 1314-13-2	-	-	-	TWA: 5 mg/m ³ STEL: 10 mg/m ³	STEL: 10 mg/m ³ TWA: 5 mg/m ³
Chemical name	Portugal	Romania	Slovakia	Slovenia	Spain
zinc oxide 1314-13-2	TWA: 2 mg/m ³ STEL: 10 mg/m ³	TWA: 5 mg/m ³ STEL: 10 mg/m ³	TWA: 1 mg/m ³ Ceiling: 1 mg/m ³	-	TWA: 2 mg/m ³ STEL: 10 mg/m ³
Chemical name	Sweden		Switzerland		United Kingdom
zinc oxide 1314-13-2	NGV: 5 mg/m ³		TWA: 3 mg/m ³ STEL: 3 mg/m ³		-

Biological occupational exposure limits This product, as supplied, does not contain any hazardous materials with biological limits established by the region specific regulatory bodies.

Derived No Effect Level (DNEL) - Workers

Chemical name	Oral	Dermal	Inhalation
zinc oxide 1314-13-2	-	83 mg/kg bw/day [4] [6]	5 mg/m ³ [4] [6] 0.5 mg/m ³ [5] [6]

[4] Systemic health effects.
[5] Local health effects.
[6] Long term.

Derived No Effect Level (DNEL) - General Public

Chemical name	Oral	Dermal	Inhalation
zinc oxide 1314-13-2	0.83 mg/kg bw/day [4] [6]	-	2.5 mg/m ³ [4] [6]

[4] Systemic health effects.
[6] Long term.

Predicted No Effect Concentration (PNEC)

Chemical name	Freshwater	Freshwater (intermittent release)	Marine water	Marine water (intermittent release)	Air
zinc oxide 1314-13-2	20.6 µg/L	-	6.1 µg/L	-	-

Chemical name	Freshwater sediment	Marine sediment	Sewage treatment	Soil	Food chain
zinc oxide 1314-13-2	117.8 mg/kg sediment dw	56.5 mg/kg sediment dw	100 µg/L	35.6 mg/kg soil dw	-

8.2. Exposure controls

Engineering controls	Ensure adequate ventilation, especially in confined areas.
Personal protective equipment	
Eye/face protection	Wear safety glasses with side shields (or goggles).
Hand protection	Wear suitable gloves.
Skin and body protection	Wear suitable protective clothing. Long sleeved clothing.
Respiratory protection	No protective equipment is needed under normal use conditions. If exposure limits are exceeded or irritation is experienced, ventilation and evacuation may be required.
General hygiene considerations	Avoid contact with skin, eyes or clothing. Wear suitable gloves and eye/face protection.
Environmental exposure controls	No information available.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state	Liquid
Appearance	Paste
Colour	white
Odour	No characteristic odour.
Odour threshold	No information available

<u>Property</u>	<u>Values</u>	<u>Remarks • Method</u>
Melting point / freezing point	No data available	None known
Initial boiling point and boiling range	No data available	None known
Flammability	No data available	None known
Flammability Limit in Air		None known
Upper flammability or explosive limits	No data available	
Lower flammability or explosive limits	No data available	

Flash point	No data available	None known
Autoignition temperature	No data available	None known
Decomposition temperature		None known
pH	No data available	None known
pH (as aqueous solution)	No data available	None known
Kinematic viscosity	No data available	None known
Dynamic viscosity	201-227 Pa s @ 20°C/68°F	None known
Water solubility	Insoluble in water	None known
Solubility(ies)	No data available	None known
Partition coefficient	No data available	None known
Vapour pressure	No data available	None known
Relative density	2.1 @ 20°C/68°F	None known
Bulk density	No data available	
Liquid Density	No data available	
Relative vapour density	No data available	None known
Particle characteristics		
Particle Size	No information available	
Particle Size Distribution	No information available	

9.2. Other information

9.2.1. Information with regards to physical hazard classes

Explosive properties	Not considered to be explosive.
Oxidising properties	Does not meet the criteria for classification as oxidizing.

9.2.2. Other safety characteristics

No information available

SECTION 10: Stability and reactivity

10.1. Reactivity

Reactivity	No information available.
------------	---------------------------

10.2. Chemical stability

Stability	Stable under normal conditions.
-----------	---------------------------------

Explosion data

Sensitivity to mechanical impact	None.
Sensitivity to static discharge	None.

10.3. Possibility of hazardous reactions

Possibility of hazardous reactions	None under normal processing.
------------------------------------	-------------------------------

10.4. Conditions to avoid

Conditions to avoid	None known based on information supplied.
---------------------	---

10.5. Incompatible materials

Incompatible materials	None known based on information supplied.
------------------------	---

10.6. Hazardous decomposition products

Hazardous decomposition products	None known based on information supplied.
----------------------------------	---

SECTION 11: Toxicological information

11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008

Information on likely routes of exposure

Product Information

Inhalation	Specific test data for the substance or mixture is not available.
Eye contact	Specific test data for the substance or mixture is not available.
Skin contact	May be absorbed through the skin in harmful amounts. Harmful in contact with skin. (based on components).
Ingestion	Specific test data for the substance or mixture is not available.

Symptoms related to the physical, chemical and toxicological characteristics

Symptoms	No information available.
----------	---------------------------

Acute toxicity

Numerical measures of toxicity

The following values are calculated based on chapter 3.1 of the GHS document

ATEmix (oral)	6,389.50 mg/kg
ATEmix (dermal)	99,999.00 mg/kg
ATEmix (inhalation-gas)	99,999.00 ppm
ATEmix (inhalation-vapour)	99,999.00 mg/l
ATEmix (inhalation-dust/mist)	5.70 mg/l

Component Information

Chemical name	Oral LD50	Dermal LD50	Inhalation LC50
zinc oxide	> 5000 mg/kg (Rat)	> 2000 mg/kg (Rat)	> 5700 mg/m ³ (Rat) 4 h

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Skin corrosion/irritation	Based on available data, the classification criteria are not met.
Serious eye damage/eye irritation	Based on available data, the classification criteria are not met.
Respiratory or skin sensitisation	Based on available data, the classification criteria are not met.
Germ cell mutagenicity	Based on available data, the classification criteria are not met.
Carcinogenicity	Based on available data, the classification criteria are not met.

Reproductive toxicity Based on available data, the classification criteria are not met.

STOT - single exposure Based on available data, the classification criteria are not met.

STOT - repeated exposure Based on available data, the classification criteria are not met.

Aspiration hazard Based on available data, the classification criteria are not met.

11.2. Information on other hazards

11.2.1. Endocrine disrupting properties

Endocrine disrupting properties The substance/mixture does not contain components considered to have endocrine disrupting properties according to REACH Article 57(f) or Commission Delegated regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605 at levels of 0.1% or higher.

11.2.2. Other information

Other adverse effects No information available.

SECTION 12: Ecological information

12.1. Toxicity

Ecotoxicity Very toxic to aquatic life with long lasting effects.

Chemical name	Algae/aquatic plants	Fish	Toxicity to microorganisms	Crustacea
zinc oxide	-	LC50: =1.55mg/L (96h, Danio rerio)	-	-

12.2. Persistence and degradability

Persistence and degradability No information available.

12.3. Bioaccumulative potential

Bioaccumulation There is no data for this product.

12.4. Mobility in soil

Mobility in soil No information available.

12.5. Results of PBT and vPvB assessment

PBT and vPvB assessment The product does not contain any substance(s) classified as PBT or vPvB above the threshold of declaration.

Chemical name	PBT and vPvB assessment
zinc oxide	The substance is not PBT / vPvB PBT assessment does not apply

12.6. Endocrine disrupting properties

Endocrine disrupting properties The substance/mixture does not contain components considered to have endocrine disrupting properties according to REACH Article 57(f) or Commission Delegated regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605 at levels of 0.1% or higher.

12.7. Other adverse effects

No information available.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Waste from residues/unused products Dispose of in accordance with local regulations. Dispose of waste in accordance with environmental legislation.

Contaminated packaging Do not reuse empty containers.

SECTION 14: Transport information

IATA

14.1 UN number or ID number UN3082
14.2 UN proper shipping name Environmentally hazardous substances, liquid, n.o.s. (zinc oxide)
14.3 Transport hazard class(es) 9
14.4 Packing group III
Description UN3082, Environmentally hazardous substances, liquid, n.o.s. (zinc oxide), 9, III
14.5 Environmental hazards Yes
14.6 Special precautions for user
Special Provisions A97, A158, A197
ERG Code 9L

IMDG

14.1 UN number or ID number UN3082
14.2 UN proper shipping name Environmentally hazardous substances, liquid, n.o.s. (zinc oxide)
14.3 Transport hazard class(es) 9
14.4 Packing group III
Description UN3082, Environmentally hazardous substances, liquid, n.o.s. (zinc oxide), 9, III, Marine pollutant
14.5 Environmental hazards Yes
14.6 Special precautions for user
Special Provisions 274, 335, 969
EmS-No F-A, S-F
14.7 Maritime transport in bulk according to IMO instruments No information available

RID

14.1 UN number or ID number UN3082
14.2 UN proper shipping name Environmentally hazardous substances, liquid, n.o.s. (zinc oxide)
14.3 Transport hazard class(es) 9
14.4 Packing group III
Description UN3082, Environmentally hazardous substances, liquid, n.o.s. (zinc oxide), 9, III
14.5 Environmental hazards Yes

14.6 Special precautions for user

Special Provisions 274, 335, 375, 601
Classification code M6

ADR

14.1 UN number or ID number UN3082
14.2 UN proper shipping name Environmentally hazardous substances, liquid, n.o.s. (zinc oxide)
14.3 Transport hazard class(es) 9
14.4 Packing group III
Description UN3082, Environmentally hazardous substances, liquid, n.o.s. (zinc oxide), 9, III, (-)
14.5 Environmental hazards Yes
14.6 Special precautions for user
Special Provisions 274, 335, 601, 375
Classification code M6
Tunnel restriction code (-)

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

National regulations

Germany

Water hazard class (WGK) obviously hazardous to water (WGK 2)

European Union

Take note of Directive 98/24/EC on the protection of the health and safety of workers from the risks related to chemical agents at work.

Authorisations and/or restrictions on use:

This product contains one or more substance(s) subject to restriction (Regulation (EC) No. 1907/2006 (REACH), Annex XVII)

Chemical name	Restricted substance per REACH Annex XVII	Substance subject to authorisation per REACH Annex XIV
zinc oxide - 1314-13-2	Use restricted. See item 75.	-

Persistent Organic Pollutants

Not applicable

Dangerous substance category per Seveso Directive (2012/18/EU)

E1 - Hazardous to the Aquatic Environment in Category Acute 1 or Chronic 1

Ozone-depleting substances (ODS) regulation (EC) 1005/2009

Not applicable

International Inventories

TSCA

Contact supplier for inventory compliance status

DSL/NDL	Contact supplier for inventory compliance status
EINECS/ELINCS	Contact supplier for inventory compliance status
ENCS	Contact supplier for inventory compliance status
IECSC	Contact supplier for inventory compliance status
KECL	Contact supplier for inventory compliance status
PICCS	Contact supplier for inventory compliance status
AIIC	Contact supplier for inventory compliance status
NZIoC	Contact supplier for inventory compliance status

Legend:

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory
DSL/NDL - Canadian Domestic Substances List/Non-Domestic Substances List
EINECS/ELINCS - European Inventory of Existing Chemical Substances/European List of Notified Chemical Substances
ENCS - Japan Existing and New Chemical Substances
IECSC - China Inventory of Existing Chemical Substances
KECL - Korean Existing and Evaluated Chemical Substances
PICCS - Philippines Inventory of Chemicals and Chemical Substances
AIIC - Australian Inventory of Industrial Chemicals
NZIoC - New Zealand Inventory of Chemicals

15.2. Chemical safety assessment

Chemical Safety Report No information available

SECTION 16: Other information

Key or legend to abbreviations and acronyms used in the safety data sheet

Full text of H-Statements referred to under section 3

H400 - Very toxic to aquatic life
H410 - Very toxic to aquatic life with long lasting effects

Legend

SVHC: Substances of Very High Concern for Authorisation:

Legend Section 8: Exposure controls/personal protection

TWA	TWA (time-weighted average)	STEL	STEL (Short Term Exposure Limit)
Ceiling	Maximum limit value	*	Skin designation
+	Sensitisers		

Classification procedure	
Classification according to Regulation (EC) No. 1272/2008 [CLP]	Method Used
Acute oral toxicity	Calculation method
Acute dermal toxicity	Calculation method
Acute inhalation toxicity - gas	Calculation method
Acute inhalation toxicity - vapour	Calculation method
Acute inhalation toxicity - dust/mist	Calculation method
Skin corrosion/irritation	Calculation method
Serious eye damage/eye irritation	Calculation method
Respiratory sensitisation	Calculation method
Skin sensitisation	Calculation method
Mutagenicity	Calculation method
Carcinogenicity	Calculation method
Reproductive toxicity	Calculation method

STOT - single exposure	Calculation method
STOT - repeated exposure	Calculation method
Acute aquatic toxicity	Calculation method
Chronic aquatic toxicity	Calculation method
Aspiration hazard	Calculation method
Ozone	Calculation method

Key literature references and sources for data used to compile the SDS

Agency for Toxic Substances and Disease Registry (ATSDR)
U.S. Environmental Protection Agency ChemView Database
European Food Safety Authority (EFSA)
European Chemicals Agency (ECHA) Committee for Risk Assessment (ECHA_RAC)
European Chemicals Agency (ECHA) (ECHA_API)
EPA (Environmental Protection Agency)
Acute Exposure Guideline Level(s) (AEGl(s))
U.S. Environmental Protection Agency Federal Insecticide, Fungicide, and Rodenticide Act
U.S. Environmental Protection Agency High Production Volume Chemicals
Food Research Journal
Hazardous Substance Database
International Uniform Chemical Information Database (IUCLID)
National Institute of Technology and Evaluation (NITE)
Australian National Industrial Chemicals Notification and Assessment Scheme (NICNAS)
NIOSH (National Institute for Occupational Safety and Health)
National Library of Medicine's ChemID Plus (NLM CIP)
National Library of Medicine's PubMed database (NLM PUBMED)
National Toxicology Program (NTP)
New Zealand's Chemical Classification and Information Database (CCID)
Organisation for Economic Co-operation and Development Environment, Health, and Safety Publications
Organisation for Economic Co-operation and Development High Production Volume Chemicals Programme
Organisation for Economic Co-operation and Development Screening Information Data Set
World Health Organization

Revision date 12/07/2023

Safety Data Sheet according to Regulation (EC) No. 1907/2006 (REACH)

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

End of Safety Data Sheet