




Passive Components > Resistors > Through-Hole Resistors



Resistor Type: **Power Resistor**

Element Type: **Thin Film**

Package Size Code: **TO220**

Power Rating: **20 W**

Resistance Class: **1k Ω – 1M Ω**

Features

Product Type Features

| | |
|-------------------|----------------|
| Resistor Type | Power Resistor |
| Element Type | Thin Film |
| Package Size Code | TO220 |

Electrical Characteristics

| | |
|-----------------------------|---------------------------|
| Power Rating | 20 W |
| Resistance Class | 1k Ω – 1M Ω |
| Resistance Value | 4.7K Ω |
| Passive Component Tolerance | 5 % |
| Operating Voltage | 500 V |

Usage Conditions

| | |
|-------------------------|------------|
| Temperature Coefficient | ±50 ppm/°C |
|-------------------------|------------|

Termination Features

| | |
|--------------------------------|--------|
| Termination Area Base Material | Copper |
| Number of Terminations | 2 |

Dimensions

| | |
|------------------------------|--------------------|
| Passive Component Dimensions | 10.6 x 4.5 x 15 mm |
|------------------------------|--------------------|

Packaging Features

| | |
|------------------|-------------------|
| Packaging Method | Loose Piece - Bag |
|------------------|-------------------|

Configuration Features



| | |
|---------------------|---|
| Number of Resistors | 1 |
|---------------------|---|

Other

| | |
|--------------------|---------------------------|
| EU RoHS Compliance | Compliant with Exemptions |
| EU ELV Compliance | Compliant with Exemptions |

Product Compliance

For compliance documentation, visit the product page on TE.com>

| | |
|---|--|
| EU RoHS Directive 2011/65/EU | Compliant with Exemptions |
| EU ELV Directive 2000/53/EC | Compliant with Exemptions |
| China RoHS 2 Directive MIIT Order No 32, 2016 | Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUN 2015 (163) SVHC > Threshold: Not Yet Reviewed |
| Halogen Content | Not Yet Reviewed for halogen content |
| Solder Process Capability | Wave solder capable to 265°C |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Customers Also Bought





TE Part #2-1879461-5
RL73H 2A R13 1% 1K RL



TE Part #2-2329328-0
PB OFF/ON HC BLU M4 TERM. IP68




TE Part #2329359-9
PB ON/OFF HC GRE M1 TERM IP68
500MM LHS




TE Part #1-1625893-3
5W SM M/OX 2% 22R



TE Part #9-2176415-0
8W STD M/OX 5% 150K



TE Part #9-2176415-1
8W STD M/OX 5% 160K



TE Part #3954384002
CGPE-105-1/2-0-SP



TE Part #20014203-12
PRESS XDCR M325M-000005-250PG



TE Part #2-2176455-5
CPF 0402 7R5 0.1% 25ppm 1K RL



TE Part #1-2176391-0
RQ 1206 15K4 0.1% 10PPM 5K RL

Documents

Datasheets & Catalog Pages

4-1773460-6_RESISTIVE_SOLUTIONS_RAIL

English

1309350_PASSIVE_COMPONENT

English

Radial Leaded High Power Resistor - Type MPR series

English

8-1773459-4_POWER_FILTERING_AND_RESISTIVE_SOLUTIONS_FOR_ELEVATORS_AND_ESCALATORS

English