




EMI & EMC Solutions > EMI Filters > Power Line Filters > Single Phase Filters > Single Phase Filters, Corcom RK Series



Current Rating: 15 A

Input Termination Type: .250" FASTON

Output Termination Type: .250" FASTON

Leakage Current (Max) (120VAC, 60Hz): .16 mA

Leakage Current (Max) (250VAC, 50Hz): .26 mA

[All Single Phase Filters, Corcom RK Series \(0\)](#)

Features

Electrical Characteristics

Current Rating	15 A
Leakage Current (Max) (120VAC, 60Hz)	.16 mA
Leakage Current (Max) (250VAC, 50Hz)	.26 mA
Operating Voltage	250 VAC

Product Type Features

Input Termination Type	.250" FASTON
Output Termination Type	.250" FASTON
Filtering Requirements	Filtered
Ground Choke Option	No

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Mechanical Attachment



Panel Mount Feature Type	Flange
--------------------------	--------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series |

Customers Also Bought




TE Part #6-6609107-7
[PS0SXDS6A=C1174](#)



TE Part #2-1415899-3
[RZ03-1C4-D024](#)



TE Part #5-2208684-3
[LEAVYSEAL Connector Housings](#)



TE Part #820193-000
[382A034-25-0](#)



TE Part #6-5530843-5
[CONN SEC II 31 POS 100C/L](#)



TE Part #1676474-2
[RN 0805 9K53 0.1% 10PPM 1KRL](#)



TE Part #G-NSDOG2-003
[AXISENSE-2 V-OUT-90 TILT SENSOR FLOOR MT](#)



TE Part #YDTS24Z15-35PAV001
[RECP ASSY](#)



TE Part #DT06-12SB-CE06
[PLG, 12P, BLK, E, SEAL RET, ENH KEY, B](#)

Documents

Product Drawings

15ERK1=F4341

English

CAD Files

Customer View Model

[ENG_CVM_CVM_2-1609089-6_G1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-1609089-6_G1.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-1609089-6_G1.2d_dxf.zip](#)

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



[1654001_CORCOM_PRODUCT_GUIDE_RK_SERIES](#)

English

[Corcom Combined Selector Charts](#)

English

[1-1654250-1_CORCOM_EMI_RFI_QRG](#)

English

[1773449-1_CORCOM_RK_SERIES_POWER_LINE_FILTER](#)

English