




Connectors > Contacts > Connector Contacts > D-Sub Connector Contacts: Pin, Brass, Signal, Size 20



Contact Type: **Pin**
Contact Mating Area Plating Material: **Gold**
Contact Retention Type Within Housing: **Snap-In**
Contact Size: **Size 20**
Wire Size: **26 – 22 AWG**

[All D-Sub Connector Contacts: Pin, Brass, Signal, Size 20 \(44\)](#)

Features

Identification Marking

Contact Color Code	Yellow
--------------------	--------

Packaging Features

Packaging Method	Loose Piece
Packaging Quantity	1000

Dimensions

Compatible Insulation Diameter Range	1.01 – 1.27 mm[.04 – .05 in]
Wire Size	.15 – .4 mm²

Mechanical Attachment

Wire Insulation Support	With
Contact Retention Type Within Housing	Snap-In

Contact Features

Contact Underplating Material	Nickel
Contact Color Bands	Yellow



Mating Pin Diameter	1.02 mm[.04 in]
PCB Contact Termination Area Plating Material	Tin
	30 µin
Contact Type	Pin
Contact Mating Area Plating Material	Gold
Contact Size	Size 20
Contact Base Material	Brass
Contact Current Rating (Max)	2 A

Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire & Cable

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part



numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 205838-1 CPC PLUG ASSEMBLY SIZE 11-8	 TE Part # 206426-1 CPC PLUG ASSEMBLY SIZE 17-3	 TE Part # 206226-1 CPC PLUG ASSEMBLY SIZE 23-7	 TE Part # 206039-1 CPC PLUG ASSEMBLY SIZE 17-28
 TE Part # 206437-1 CPC PLUG ASSEMBLY SIZE 23-57	 TE Part # 206136-1 CPC PLUG ASSEMBLY SIZE 23-7	 TE Part # 206485-1 CPC PLUG ASSEMBLY SIZE 11-9	 TE Part # 206434-1 CPC PLUG ASSEMBLY SIZE 11-8
 TE Part # 206126-1 CPC PLUG ASSEMBLY SIZE 17-28	 TE Part # 91525-1 CCII AMPLIMITE HDP-20 PIN SKT 26-22 ASSY		


Customers Also Bought

 TE Part #205206-8 D-Sub Crimp: Plug, Signal, 15 Posn, Pin Size 20, Shell Size 2	 TE Part #1658615-2 25 POS HDF PLUG, AP, LEAD FREE	 TE Part #1658614-2 25 POS HDF RCPT, AP, LEAD FREE	 TE Part #1658537-1 SOCKET CONT DUPL PLT STRIP HD-
--	--	--	--






TE Part #1658539-3
PIN CONT DUPL PLT LP HD-20 AMP



TE Part #206358-5
CABLE CLAMP ASY, SIZE 11



TE Part #5745171-2
SIZE 1 ASSY KIT .200



TE Part #5748677-1
PLTD PLST CBL CLMP KIT,SZ 1

Documents

Product Drawings

PIN CONT DUPL PLT LP HD-20 AMP

English

CAD Files

Customer View Model

ENG_CVM_CVM_1658544-1_E.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1658544-1_E.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1658544-1_E.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMP Circular Connectors for Commercial Signal & Power Applications

English

Signal Contacts

English

AMPLIMITE Subminiature D Connectors - Cable Connectors

English

AMPLIMITE Cable Connectors and Shielding Hardware Kits QRG

English

Product Specifications

Application Specification

English

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

1658544-1

Pin Contact, Gold, Snap-In Contact Retention, Size 20 Contact Size, 26 – 22 AWG
Wire Size, .15 – .4 mm² Wire Size, Crimp, Brass, Signal



English