



**Part Number :** [1200660975](#)  
**Product Description :** Micro-Change (M12)  
Double-Ended Cordset, 4 Poles, Male  
(Straight) to Female (90°), 18 AWG, Yellow TPE  
Cable, 1.50m (4.92') Length  
**Series Number :** 120066  
**Status :** Active  
**Product Category :** Circular Industrial  
Cordsets  
**Engineering Number :** 884031K03M015




Documents & Resources

Drawings  
[1200660975\\_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

---

### Part Details

#### General

Status	Active
Category	Circular Industrial Cordsets
Series	120066
Description	Micro-Change (M12) Double-Ended Cordset, 4 Poles, Male (Straight) to Female (90°), 18 AWG, Yellow TPE Cable, 1.50m (4.92') Length
IP Rating	IP67
Product Name	Micro-Change (M12)
Type	Double Ended
UPC	78678845336

#### Agency

CSA	LR6837
UL	E152210

#### Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

#### Physical

Cable Diameter	7.14mm (.281")
Cable Length	1.50m (4.92')
Color - Cable Jacket	Yellow
Connector End A	Micro-Change (M12)
Connector End B	Micro-Change (M12)
Coupling Style	Threaded
Gender	Female-Male
Keyway	Single
LED Indicator	None

Material - Cable Jacket	TPE
Material - Connector Body	TPE
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	124.000/g
Orientation	90° to Straight
Poles	4
Temperature Range - Operating	-20° to +105°C
Wire/Cable Type	PLTC/ITC
Wire Size (AWG)	18