



Sensors > Pressure Sensors > Media Isolated Pressure Sensors > 19MM MV OUTPUT PRESSURE SENSOR



Pressure Sensor Type: **mV Output Pressure Sensors**

Pressure Type: **Gauge**

Output Signal Type: **100mV**

Operating Temperature Range: **-40 – 125 °C [ -40 – 257 °F ]**

Sensor Package: **O-Ring Mount**

[All 19MM MV Output Pressure Sensor \(41\)](#)

Features

Product Type Features

Pressure Sensor Type	mV Output Pressure Sensors
Pressure Type	Gauge
Sensor Package	O-Ring Mount

Configuration Features

Electrical Connection	Cable w/ Connector
-----------------------	--------------------

Electrical Characteristics

Supply Current	1.5 mA
----------------	--------

Dimensions

Product Diameter	19 mm[.748 in]
Product Height	6.48 mm[.25 in]

Usage Conditions

Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Proof Pressure Range	3X
Output Signal Type	100mV



Other

Non-Linearity ±	.1 %
Sensor Options	No Tube

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2023 (235) SVHC > Threshold: Methanone, (diphenylphosphinyl)(2,4,6-trimethylphenyl)- (1% in Component a) <b>Article Safe Usage Statements:</b> Wash thoroughly after handling. Do not handle until all safety precautions have been read and understood. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | MEAS 82



Customers Also Bought



Documents

- CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_82-015G-C\_H.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_82-015G-C\_H.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_82-015G-C\_H.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



82C

English