




Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal Type: **Tab**
Connector & Housing Type: **Tab Housing**
Number of Positions: **4**
Terminal Orientation: **Straight**
Primary Product Color: **Red**

Features

Contact Features

Terminal Type	Tab
Terminal Orientation	Straight
Contact Mating Retention	With

Product Type Features

Connector & Housing Type	Tab Housing
Sealable	No

Configuration Features

Number of Positions	4
---------------------	---

Body Features

Primary Product Color	Red
-----------------------	-----

Housing Features

Housing Material	Polyamide 6.6 GF
Centerline (Pitch)	5 mm[.197 in]

Mechanical Attachment

--	--



Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)
Mating Alignment Type	Keyed

Packaging Features

Packaging Method	Loose Piece
Packaging Quantity	800

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Dimensions

Product Height	28.6 mm[1.13 in]
----------------	------------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2017 (173) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the



product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Customers Also Bought

TE Part #2151582-1
OCEAN_2.0_Applicator-S-110F165O-RSM

TE Part #215882-6
AMP-LATCH MIL TYPE RCPT CONNECTOR

TE Part #2836077-1
OCEAN_2.0_Applicator-S-070F100O-RSM

TE Part #7-2150373-7
OCEAN-055F080F-CRIMPTOOLINGKIT

KIT
TE Part #7-2266813-7
OCEAN_2.0_SPARE_PART_KIT-055F062F

KIT
TE Part #7-2837932-7
OCEAN_2.0_SPARE_PART_KIT-062F091O

TE Part #926298-5
UN-MNL STECK-GEH 4P

TE Part #886281-000
FLHTC0311-26-2

Documents

Product Drawings

HOUSING TAB 5MM 4 P RED

English

CAD Files

Customer View Model

ENG_CVM_2-144836-4_B.3d_igs.zip

English

Customer View Model

ENG_CVM_2-144836-4_B.3d_stp.zip

English

Customer View Model

ENG_CVM_2-144836-4_B.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.