




Terminals & Splices > Automotive Terminals > TIMER, RECEPTACLE AND TAB



Terminal Type: **Receptacle**

Wire Size: **13 – 11 AWG**

Mating Tab Width: **2.8 mm [.11 in]**

Interface Plating: **Tin (Sn)**

[All TIMER, RECEPTACLE AND TAB \(279\)](#)

Features

Product Type Features

Receptacle Style	180°
Primary Locking Feature	Locking Lance
Sealable	No

Contact Features

Typical Current Rating	30 A
Crimp Type	F-Crimp
Contact Size	2.8mm
Contact Fabrication	Stamped & Formed
Wire Contact Termination Area Plating Material	Tin
Terminal Type	Receptacle
Mating Tab Width	2.8 mm[.11 in]
Interface Plating	Tin (Sn)
Mating Tab Thickness	.8 mm[.031 in]

Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire

Dimensions

--	--



Compatible Insulation Diameter Range	2.7 – 3.7 mm[.106 – .145 in]
Wire Size	13 – 11 AWG
Wire Size Search	2.5 mm², 3 mm², 4 mm²
Tab Length	19.5 mm[.77 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature (Max)	130 °C[266 °F]
Operating Temperature Range	-40 – 130 °C[-40 – 266 °F]

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Industry Standards

Compatible With Agency/Standards Products	IEC 664/664A (DIN VDE 0110)
---	-----------------------------

Packaging Features

Packaging Method	Reel
Packaging Quantity	2700

Other

Terminal Transmits	25 – 40 A (Power)
--------------------	-------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-444017-1
HSG ASSY TIMER 9P




TE Part # 2266277-2
OCEAN-2.0-APPLICATOR-S-120F160OV-RSA



TE Part # CAT-T4827-CH8172
Timer Connector Housing




TE Part # 7-2266277-7
OCEAN_2.0_SPARE_PART_KIT-120F160OV



TE Part # 444017-2
HSG ASS'Y 9 POS JR



TE Part # 1801773-1
FUSES AND RELAYS HOLDER 6 MINIFUSES V2



TE Part # 9-1579008-2
EXTRACTION TOOL



TE Part # 2266277-1
OCEAN-2.0-APPLICATOR-S-120F160OV-RSM



TE Part # 9-1579018-4
EXTRACTION TOOL



TE Part # 2305570-1
Strip Terminal Cutter-Side Feed-No Crimp



TE Part # 1-1579007-6
EXTRACTION TOOL

Also in the Series | Junior Power Timer



Automotive Connector Caps & Covers (9)



Automotive Connector Locks & Position Assurance(8)



Automotive Housings(285)




Automotive Terminals(153)



Busbars & Terminals(1)



Connector Seals & Cavity Plugs(7)



Module Components(1)



Other Automotive Connector Accessories(2)



Special Purpose Terminals(2)

Customers Also Bought



TE Part #1801614-3
4 MINIFUSES CLIPSHUNT (2,5-4)



TE Part #1801432-1
RCPT CONT, 8MM NG1+, MAXIFUSE, 5-6 MM2




TE Part #1801431-1
RCPT CONT, 8MM NG1+, MAXIFUSE, 2.5-4 MM2



TE Part #4-953892-1
16/8W+4SC MQS SOCKET HSG



TE Part #626094-1
TERMINAL, .250 FASTIN-ON REC



TE Part #1379668-2
24W PLUG HSG ASSY grey



TE Part #1801619-1
RELAY 70A HOLDER



TE Part #1801618-1
RELAY 40A HOLDER



Documents

Product Drawings

JPT A REC 2.8 Contact SRC Sn

English

JPT A REC 2.8 Contact SRC Sn

English

CAD Files

Customer View Model

ENG_CVM_1241978-2_B9.3d_igs.zip

English

Customer View Model

ENG_CVM_1241978-2_B9.3d_stp.zip

English

Customer View Model

ENG_CVM_1241978-2_B9.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

German

Application Specification

English

Application Specification

English