




Terminals & Splices > PCB Terminals



PCB Terminal Type: **Tab**
Mating Tab Width: **6.35 mm [.25 in]**
Mating Tab Thickness: **.81 mm [.032 in]**
PCB Hole Diameter: **3.3 mm [.13 in]**
Termination Method to PCB: **Through Hole - Screw**

Features

Product Type Features

Terminal Features	Stud Hole
Insertion Force	Normal

Contact Features

PCB Contact Termination Area Plating Material Thickness	1.01 μm[40 μin]
Contact Mating Area Plating Material Thickness	1.01 μm[40 μin]
PCB Terminal Type	Tab
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Plating Material	Tin
Contact Underplating Material	None
Terminal Size	6.35
Terminal Orientation	Vertical

Termination Features

Termination Method to PCB	Through Hole - Screw
---------------------------	----------------------



Product Terminates To

Printed Circuit Board

Dimensions

Stud Diameter	3.3 mm[.13 in]
PCB Hole Diameter	3.3 mm[.13 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-30 – 110 °C[-22 – 230 °F]

Packaging Features

Packaging Quantity	1000
Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts











 TE Part # 41482 250 FASTON TAB TPBR	 TE Part # 41480 250 FASTON TAB TPBR	 TE Part # 42117-2 250 FASTON TAB TPBR	 TE Part # 41290 250 FASTON,TAB,BR
 TE Part # 1217558-2 250 FASTON,TAB,TPBR	 TE Part # 41484 250 FASTON TAB TPBR	 TE Part # 42095-1 250 FASTON TAB TPBR	 TE Part # 41292 250 FASTON,TAB,BR
 TE Part # 41481 250 FASTON TAB TPBR	 TE Part # 41291 250 FASTON,TAB,BR	 TE Part # 62261-1 250 FASTON TAB BR	

Also in the Series | FASTON 250

 Compression Connectors(4)	 Crimp Terminal Housings(132)	 Insertion & Extraction Tools(6)	 Magnet Wire Terminals(1)
 PCB Terminals(134)	 Quick Disconnects(425)	 Splices(4)	

Customers Also Bought



 <p>Single Wall</p> <p>TE Part #753895-000 82A0111-12-9</p>	 <p>TE Part #5555077-1 MJ,LPF,R/A,6P/6C,SMT,PNL STOP</p>	 <p>TE Part #1-2834021-3 3POS 2.5MM TES CONN.</p>	 <p>TE Part #320749 SOLIS SPDFLG 22-16COM22-18MIL6</p>
 <p>TE Part #485893-2 004 HOUSING FFC PIN 100CL SR</p>	 <p>TE Part #197127-000 Busbar Insulation Tubing up to 35 kV</p>	 <p>TE Part #1-967622-6 Timer Connector Housing</p>	 <p>TE Part #11027289-00 44011RC-BP,THERM,ROHS</p>

Documents

Product Drawings

250 FASTON TAB TPBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_42506-2_M.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_42506-2_M.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_42506-2_M.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

FASTON Tabs

English

Product Specifications

Application Specification

English

Agency Approvals

CSA Certificate



English

[CSA Certificate](#)

English