

Page 1 of 5 **SDS-E-G100L** 

1

Prepared to OSHA, ACC, ANSI, NOHSC, WHMIS, GHS & EU Standards

SDS Revision: 5.2

1.1	Product Name:										o /=	<u></u>	4.0.01	
	Floduct Name.	DEOXIT	® GOLD G-8	SERIES, 1	100%	SO	LUT	ION,	0%	VO	С (Р	/N G	100L	)
1.2	Chemical Name:	NA												
1.3	Synonyms:		OLD G-Series; PN											
1.4	Trade Names:	Part No. G1 Part No. G1 Part No. G5 Part No. G5 Part No. G1 Part No. G1 Part No. G1	0W (50 wipes) 00FW-3X3 (100 wij 00L-12 (354 ml) 00L-16 (472 ml)	P (2 ml);	Part Part Part Part Part Part	No. G No. G No. G No. G No. G No. G	100L-1 100L-F 50FW 100L-2 100L-1 100L-3	2C (12 26C (6 (50 wip 2 (59 m 3 (384 2 (944	2 ml) ml) bes) l) ml) ml)		Part N Part N Part N Part N Part N	o. G1W o. G100 o. G100 o. G100 o. G100	' (single )W-3X3 )L-8 (23 )L-13HF )L-9L (9	(100 wipes) 66 ml) PE (384 ml) 9 L)
1.5	Product Use:		00L-8G (30 L)			No. G			<b>U</b> /		Part N	0. G100	)L-SWF	10
1.6	Distributor's Name:	CAIG Labora	enhancer for plate	a ana gola pia	lea ele	Suonic	contac		nneci	ors				
1.7	Distributor's Address:		her Court, Poway,	CA 92064-687	76 USA									
1.8	Emergency Phone:		EC: +1 (703) 5				1 020		2020	5206	<u>۱</u>			
1.9	Business Phone / Fax:			21-3001 // 1	-1 (00	0) 424	4-930		JNZU	5200	)			
1.9	Dusiness Flione / I ax.	+1 (800) 224	1-4123											
			2 4/7	ARDS ID	FNT	IFIC	ΔΤΙΛ	אר						
2.1	Hazard Identification:	Canadian W DeoxIT <sup>®</sup> 100 WARNING!	accordance with U HMIS, and Australi % solution is non-v CAUSES EYE IRF o: Eve Irritant 2B	an Work Healt olatile and nor	h and S	Safety (			nded to	o com	ply wit	h OSH	A 29 C	FR 1910.120
2.2	Label Elements:	Classification: Eye Irritant 2B         Hazard Statements (H): H320 – Causes eye irritation.         Precautionary Statements (P): P264 – Wash thoroughly after handling. P305+P351+P338 – IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. P337+P317 – If eye irritation persists: Get medical help.       NO PICTOGRAM												
2.3	Other Warnings:		OF REACH OF CH		геуетп	ιαιοπ	persisi	.s. 0ei	medic	arnen	<i>.</i>			
		KEEP OUT		ILDREN										
		3 0	OMPOSITIO		וחשכ		INF		/ ^ T					
		<u> </u>										I AIR (mg	/m <sup>3</sup> )	
							GIH om	ES-	NOHSC ppm ES-			OSHA ppm		
		CAS No.		EINECS No.	%	TLV	STEL	TWA	STEL	PEAK	PEL	STEL	IDLH	OTHER
eox	IT <sup>®</sup> GOLD G-Series		NA o. Non-Hazardous/Pr	NA	100	NA	NA	NF	NF	NF	NA	NA	NA	
100		REACTINES. N	0. NON-Hazardous/11	ophetary										
			1 E	IRST AID			DEC							
4.1	First Aid:	Ingestion:	If ingested, do n IMMEDIATELY. unconscious pers estimate of the swallowed. Splashes are not	not induce vo If the patient i son. Contact t time at which	miting. s vomit he nea the m	lf pr ing, co rest Po aterial	oduct ontinue oison C was i	to offe control ngeste	er wate Cente d and	erorm rorloo the a	nilk. N cal em amoun	lever gi ergenc t of the	ve wate y numb e subst	er or milk to a er. Provide a ance that wa
		<u>Skin</u> :	for at least 15 mir Wash thoroughly least 15 minutes.							diately	flush	skin wit	h plenty	of water for
		Inhalation:	Remove victim to artificial respiratio	on. Keep perso	on warr	n, quiet	t and g	et med	dical at	tentior		f breath	ing stop	os give
4.2	Effects of Exposure:	Ingestion:         If product is swallowed, may cause nausea, vomiting and/or diarrhea.           Eyes:         Moderately irritating to the eyes. Symptoms of overexposure may include redness, itching, irritation and watering.           Skin:         May be irritating to skin. The product can cause allergic skin reactions (e.g., rashes, welts, dermatitis) in some sensitive individuals.												
	Symptoms of Overexposure:	Inhalation:	None expected.	l discomfort y	omiting	and/or	diarrh	62						
4.3	or or or or or one posule.	Eves:       Overexposure in eyes may cause redness, itching and watering.         Skin:       Symptoms of skin overexposure may include redness, itching, and irritation of affected areas. Frostbite like symptoms. The product can cause allergic skin reactions (e.g., rashes, welts, dermatitis) in some												
4.3		<u>Skin</u> :							actions	6 (e.g.,	rashe	es, welt	s, dern	natitis) in son



Page 2 of 5 **SDS-E-G100L** 

Prepared to OSHA, ACC, ANSI, NOHSC, WHMIS, GHS & EU Standards

SDS Revision: 5.2 SDS

		4. FIRST A	AID ME	EASU	RES –	cont'	d				
4.5	Chronic Health Effects:	Non-irritating when used as directed. Overexposure may trigger asthma-like symptoms in some sensitive individuals May also induce skin sensitization and respiratory hypersensitivity. Possible allergic dermatitis.									
4.6	Target Organs:	Eyes, Skin.									
4.7	Medical Conditions Aggravated by Exposure:	Pre-existing dermatitis, other ski	n conditio	ons, and	disorders	of the	HEALTH	H			1
	35 7 1	target organs (eyes, skin).					FLAMM	ABILITY	ſ		0
							PHYSIC	AL HAZ	ZARDS		0
							PROTE	CTIVE E		IENT	В
							EYES	SKIN			
		5. FIREI	FIGHT		IEASU	RES					
5.1	Fire & Explosion Hazards:	This product is not flammable. He temperatures to form toxic gases (	owever, it	f involved			luct may d	ecompos	e at higl	۱	
5.2	Extinguishing Methods:	Water, Foam, CO <sub>2</sub> , Dry Chemical.			to cool un	opened o	containers.				
5.3	Firefighting Procedures:	Fight fires for surrounding materia breathing apparatus (pressure-de after the fire is out. Use water sp fire upwind. Avoid spraying wate Prevent runoff from fire control of any natural waterway. Firefighter pressure self-contained breathing decomposition products and oxyge	mand) ar oray to co r directly r dilution rs must u apparatu	nd full pro ool fire-ex into stora from ent ise full b us to prof	otective ge posed sur age contai ering sewe unker gea	ear. Ke rfaces ar iners bec ers, draii r includir	ep contain id to protectause of da ns, drinking ng NIOSH-	ers cool ct person anger of g water s approved	until we al. Figh boil-over upply, o d positive	ll t r e	
-		6. ACCIDEN	TAL R	ELEA	SE ME	ASU	RES				
6.1	Spills:	Before cleaning any spill or leak, individuals involved in spill cleanup must wear appropriate Personal Protective Equipment. Plastic or rubber gloves, respirator, eye protection and apron may be required for clean-up of large spills. <u>Small Spills</u> : Wear appropriate protective equipment including gloves and protective eyewear. Use a non-combustible material such as vermiculite or sand to soak up the product and place it into a container for later disposal. Do not use water or a material such as "speedy dry" to soak up material. Sweep up material using non-sparking materials (e.g., plastic brooms, shovels, dustpans) and place into a plastic container or plastic liner within another container. Large Spills: Keep incompatible materials (e.g., organics such as oil) away from spill. Stay upwind and away from spill or release. Isolate immediate hazard area and keep unauthorized personnel out of area. Stop spill or release if it can be done with minimal risk. Wear appropriate protective equipment including respiratory protection as conditions warrant.									
	1	7. HANDLING									
7.1	Work & Hygiene Practices:	Do not eat, drink or smoke when necessary. Use chemical goggles	s if eye co	ntact is p	ossible. V	Nash uni	ntentional	residues	with soa	p and w	arm water.
7.2	Storage & Handling:	Use and store in a cool, dry, we sunlight. Avoid temperatures abordamage.	ell-ventilat ve 120 °F	ed locati . Keep a	on (e.g., l away from	ocal exh incompa	aust ventil tible subst	ation, far ances. P	ns) away Protect co	/ from h ontainers	eat and direct s from physical
7.3	Special Precautions:	Clean all spills promptly. Spilled n	naterial m	nay prese	nt a slippi	ng hazar	d.				
		8. EXPOSURE CONT	ROLS	& PE	RSON		ROTEC				
8.1	Exposure Limits:		ACC			NOHSC			OSHA	<u>.                                    </u>	OTHER
	ppm (mg/m <sup>3</sup> )	CHEMICAL NAME(S)		STEL	ES-TWA	ES- STEL	ES- PEAK	PEL	STEL		
8.2	Ventilation & Engineering Controls:	NA         NA<									
8.3	Respiratory Protection:	No special respiratory protection is required under typical circumstances of use or handling. In instances where dusts of this product are generated, and respiratory protection is needed, use only protection authorized by 29 CFR §1910.134, applicable U.S. State regulations, or the Canadian CAS Standard Z94.4-93 and applicable standards of Canadian Provinces, EC member States, or Australia.									
8.4	Eye Protection:	Avoid eye contact. None required handling or using large quantities	of this pro	oduct.			, 0				
8.5	Hand Protection:	None required under normal con individuals. When handling large plastic gloves.	quantities	s (e.g., ≥	1 gallon	(3.8 L)),	wear rubb	er, nitrile	or impe	rvious	
8.6	Body Protection:	wash stations and deluge showe	Plastic gloves. No apron required when handling small quantities. When handling large quantities (e.g., ≥ 5 lbs), eye wash stations and deluge showers should be available. Upon completion of work activities involving large quantities of this product, wash any exposed areas thoroughly with soap and water.								



Page 3 of 5 **SDS-E-G100L** 

Prepared to OSHA, ACC, ANSI, NOHSC, WHMIS, GHS & EU Standards

SDS Revision: 5.2

Appearance:	9. PHYSICAL & CHEMICAL PROPERTIES
Odor:	Ethereal / hydrocarbon odor
	NA
	NA
•	NA
Initial Boiling Point/Boiling	>220 °C (428 °F)
	>250 °C (482 °F)
Upper/Lower Flammability	NA
	< 0.1 mm Hg @ 20 °C (68 °F)
•	NA
	0.870
,	Soluble
*	NA
	NA
Į į	NA
	5.4-7.5 cSt @ 104 °F NA
	NA
	10. STABILITY & REACTIVITY
Stability:	Stable under normal conditions unstable with heat or contamination.
Hazardous Decomposition Products:	Oxides of carbon (CO, CO <sub>2</sub> ).
Hazardous Polymerization:	Will not occur.
Conditions to Avoid:	Open flames, sparks, high heat, incompatible substances and direct sunlight.
Incompatible Substances:	Avoid extreme heat and ignition sources. Store away from oxidizers.
	11. TOXICOLOGICAL INFORMATION
Poutos of Entry:	
Toxicity Data:	Inhalation:         YES         Absorption:         YES         Ingestion:         NO           This product has NOT been tested on animals to obtain toxicology data. Toxicology data, found in scientific literature, is         Infestion:         NO
	available for some of the components of the product and is not presented in this document.
	Moderate irritation to eyes and skin near affected areas.
	This material may aggravate any pre-existing skin condition (e.g., dermatitis).
	No.
Reproductive Toxicity:	This product is not reported to produce reproductive toxicity in humans.
Mutagenicity:	This product is not reported to produce mutagenic effects in humans.
Embryotoxicity:	This product is not reported to produce embryotoxic effects in humans.
Teratogenicity:	This product is not reported to cause teratogenic effects in humans.
Reproductive Toxicity:	This product is not reported to cause reproductive effects in humans.
Irritancy of Product:	The product can cause allergic skin reactions (e.g., rashes, welts, dermatitis) upon prolonged or repeated exposure.
Biological Exposure Indices:	NE
Physician Recommendations:	Treat symptomatically.
	12. ECOLOGICAL INFORMATION
Environmental Stability:	There is no specific data available for this product.
Effects on Plants & Animals:	There is no specific data available for this product.
Effects on Aquatic Life:	There is no specific data available for this product however, very large releases of this product may be harmful or fatal to
	overexposed aquatic life.
	13. DISPOSAL CONSIDERATIONS
Waste Disposal:	Disposal should be in accordance with local, state and federal regulations. Dispose of in accordance with federal, state and local regulations.
	Odor Threshold: pH: Melting Point/Freezing Point: Initial Boiling Point/Boiling Range: Flashpoint: Upper/Lower Flammability Limits: Vapor Density: Relative Density: Relative Density: Solubility: Partition Coefficient (log Pow): Autoignition Temperature: Decomposition Temperature: Viscosity: Other Information: Stability: Hazardous Decomposition Products: Hazardous Delymerization: Conditions to Avoid: Incompatible Substances: Routes of Entry: Toxicity Data: Acute Toxicity: Chronic Toxicity: Suspected Carcinogen: Reproductive Toxicity: Mutagenicity: Embryotoxicity: Teratogenicity: Reproductive Toxicity: Irritancy of Product: Biological Exposure Indices: Physician Recommendations: Environmental Stability: Effects on Plants & Animals:



Page 4 of 5 **SDS-E-G100L** 

Prepared to OSHA, ACC, ANSI, NOHSC, WHMIS, GHS & EU Standards

SDS Revision: 5.2

		14. TRANSPORTATIO			
The	basic description (ID Numl		n, packing group) is shown for each mode of transportation. Add	ditional	
desc	riptive information may be	required by 49 CFR, IATA/ICAO, IMDG and the C	TDGR.		
14.1	49 CFR (GND):	NOT REGULATED			
14.2	IATA (AIR):	NOT REGULATED			
14.3	IMDG (OCN):	NOT REGULATED			
14.4	TDGR (Canadian GND):	NOT REGULATED			
14.5	ADR/RID (EU):	NOT REGULATED			
14.6	SCT (MEXICO):	NOT REGULATED			
14.7	ADGR (AUS):	NOT REGULATED			
		15. REGULATORY I	NFORMATION		
15.1	SARA Reporting Requirements:		ubject to SARA Title III, section 313 reporting requirements.		
15.2	SARA TPQ:	There are no specific Threshold Planning Quant			
15.3	TSCA Inventory Status:	The components of this product are listed on the			
15.4	CERCLA Reportable Quantity:	NA			
15.5	Other Federal Requirements:	NA			
15.6	Other Canadian Regulations:	NA This product has been classified according to the hazard criteria of the Controlled Products Regulations (CPR) and the SDS contains all of the information required by the CPR. The components of this product are listed on the DSL/NDSL. None of the components of this product are listed on the Priorities Substances List.			
15.7	State Regulatory Information:	criteria lists: California Proposition 65 (CA65), List (FL), Massachusetts Hazardous Substar Hazardous Substances List (MN), New Jersey Pennsylvania Right-to-Know List (PA), Was Substances List (WI).	ncentration of 1.0% or greater, are listed on any of the following Delaware Air Quality Management List (DE), Florida Toxic Subs nces List (MA), Michigan Critical Substances List (MI), Min Right-to-Know List (NJ), New York Hazardous Substances Lis shington Permissible Exposures List (WA), Wisconsin Haz nown to the State of California to cause cancer, birth defects, o	stances nnesota st (NY), zardous	
15.8	Other Requirements:	NA	ww.r oowanings.ca.gov.		
		16. OTHER INFO	ORMATION		
16.1	Other Information:	WARNING! CAUSES EYE IRRITATION. Use only as directed. Avoid contact with ey immediately (show the label where possible). If KEEP OUT OF REACH OF CHILDREN.	es. In case of accident or if you feel unwell seek medical skin irritation occurs: Get medical help.	advice	
16.2	Terms & Definitions:	See last page of this Safety Data Sheet.			
16.3	Disclaimer:	This Safety Data Sheet is offered pursuant to C government regulations must be reviewed fo Laboratories, Inc.'s knowledge, the information accuracy, suitability or completeness is not gual provided. The information contained herein rel- other materials, all component properties must consult the latest edition.	DSHA's Hazard Communication Standard, 29 CFR §1910.1200. r applicability to this product. To the best of ShipMate's & n contained herein is reliable and accurate as of this date ho ranteed and no warranties of any type, either expressed or impli- ates only to the specific product(s). If this product(s) is combine be considered. Data may be changed from time to time. Be s	& CAIG owever, ied, are ied with	
16.4	Prepared for:	CAIG Laboratories, Inc. 12200 Thatcher Court Poway, CA 92064-6876 Tel: +1 (800) CAIG-123 (244-4123) Fax: +1 (858) 486-8398 fax http://www.caig.com/	CANGE LABORATORIES, INC.		
16.5	Prepared by:	ShipMate, Inc. P.O. Box 787 Sisters, Oregon 97759-0787 USA Tel: +1 (310) 370-3600 Fax: +1 (310) 370-5700 http://www.shipmate.com	ShipMate Dangerous Goods Training & Consulting		



Page 5 of 5 SDS-E-G100L

Prepared to OSHA, ACC, ANSI, NOHSC, WHMIS, GHS & EU Standards

SDS Revision: 5.2

SDS Revision Date: 11/16/2024

### **DEFINITION OF TERMS**

A large number of abbreviations and acronyms appear on a SDS. Some of these that are commonly used include the following:

#### GENERAL INFORMATION:

CAS No.	Chemical Abstract Service Number
RTECS No.	Registry of Toxic Effects of Chemical Substances Number
EINECS No.	European Inventory of Existing Commercial Chemical Substances Number
EINE OO NO.	European inventory of Existing Commercial Chemical Substances Number

#### EXPOSURE LIMITS IN AIR:

ACGIH	ACGIH American Conference on Governmental Industrial Hygienists		
IDLH	Immediately Dangerous to Life and Health		
NOHSC National Occupational Health and Safety Commission (Australia)			
OSHA U.S. Occupational Safety and Health Administration			
PEL	Permissible Exposure Limit		
STEL	Short Term Exposure Limit		
TLV	Threshold Limit Value		
TWA	Time Weighted Average		

#### FIRST AID MEASURES:


CPR	Cardiopulmonary resuscitation - method in which a person whose heart has
	stopped receives manual chest compressions and breathing to circulate blood
	and provide oxygen to the body.

#### HAZARDOUS MATERIALS IDENTIFICATION SYSTEM: HMIS

### HEALTH, FLAMMABILITY & REACTIVITY RATINGS:

0	Minimal Hazard	HEALTH
1	Slight Hazard	FLAMMABILITY
2	Moderate Hazard	PHYSICAL HAZARDS
3	Severe Hazard	PERSONAL PROTECTION
4	Extreme Hazard	

### PERSONAL PROTECTION RATINGS:



#### OTHER STANDARD ABBREVIATIONS:


Carc	Carcinogenic
Irrit	Irritant
NA	Not Available
NR	No Results
ND	Not Determined
NE	Not Established
NF	Not Found
SCBA	Self-Contained Breathing Apparatus
Sens	Sensitization
STOT RE	Specific Target Organ Toxicity – Repeat Exposure
STOT SE	Specific Target Organ Toxicity – Single Exposure

## FLAMMABILITY LIMITS IN AIR: Autoignition Temperature Minimum temperature required to initiate combustion in air with no other of ignition

Autoignition Temperature	Minimum temperature required to initiate combustion in air with no other source of ignition
LEL	Lower Explosive Limit - lowest percent of vapor in air, by volume, that will explode or ignite in the presence of an ignition source
UEL	Upper Explosive Limit - highest percent of vapor in air, by volume, that will explode or ignite in the presence of an ignition source

#### HAZARD RATINGS:

0	Minimal Hazard	FLA
1	Slight Hazard	FLA
2	Moderate Hazard	
3	Severe Hazard	
4	Extreme Hazard	
ACD	Acidic	•
ALK	Alkaline	
COR	Corrosive	/
W	Use No Water	HEA
ох	Oxidizer	
TREEOII	Radioactive	



#### TOXICOLOGICAL INFORMATION:

LD <sub>50</sub>	Lethal Dose (solids & liquids) which kills 50% of the exposed animals
LC <sub>50</sub>	Lethal concentration (gases) which kills 50% of the exposed animal
ppm	Concentration expressed in parts of material per million parts
TD <sub>io</sub>	Lowest dose to cause a symptom
TCLo	Lowest concentration to cause a symptom
TD <sub>io</sub> , LD <sub>io</sub> , & LD <sub>o</sub> or	Lowest dose (or concentration) to cause lethal or toxic effects
TC, TC <sub>o</sub> , LC <sub>io</sub> , & LC <sub>o</sub>	
IARC	International Agency for Research on Cancer
NTP	National Toxicology Program
RTECS	Registry of Toxic Effects of Chemical Substances
BCF	Bioconcentration Factor
TLm	Median threshold limit
log Kow or log Koc	Coefficient of Oil/Water Distribution

### **REGULATORY INFORMATION:**

WHMIS	Canadian Workplace Hazardous Material Information System
DOT	U.S. Department of Transportation
тс	Transport Canada
EPA	U.S. Environmental Protection Agency
DSL	Canadian Domestic Substance List
NDSL	Canadian Non-Domestic Substance List
PSL	Canadian Priority Substances List
TSCA	U.S. Toxic Substance Control Act
EU	European Union (European Union Directive 67/548/EEC)
WGK	Wassergefährdungsklassen (German Water Hazard Class)

### CLP/GHS (1272/2008/EC) PICTOGRAMS:

			$\Diamond$	<b>F</b>		$\diamondsuit$		
GHS01	GHS02	GHS03	GHS04	GHS05	GHS06	GHS07	GHS08	GHS09
Explosive	Flammable	Oxidizer	Pressurized	Corrosive	Toxic	Harmful Irritating	Health Hazard	Environment