

NBC-PP-J1PGY-S/R4GC8 - DIN rail adapter



1769127

<https://www.phoenixcontact.com/in/products/1769127>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail adapter, degree of protection: IP20, number of positions: 8, 10 Gbps, CAT6_A

Your advantages

- Compact design
- For distributing copper and fiber optic cabling
- Front release without special tool
- One-Piece Design
- Assembly without special tools
- Optional overall shielding braid for copper modules
- Security elements available as accessories
- Adapter-less integration of module inserts
- Marking service: Phoenix Contact can custom-mark all labels according to your requirements

Commercial data

Item number	1769127
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	ABNLAA
GTIN	4067923380448
Weight per piece (including packing)	42.2 g
Weight per piece (excluding packing)	42.2 g
Country of origin	DE

NBC-PP-J1PGY-S/R4GC8 - DIN rail adapter



1769127

<https://www.phoenixcontact.com/in/products/1769127>

Set consists of

NBC-PP-G1PGY - DIN rail adapter

1041740

<https://www.phoenixcontact.com/in/products/1041740>



DIN rail adapter, design: Headers with shielding, degree of protection: IP20, material: PC-GF10, connection method: Quick connection, without assembled modules

CUC-I-D1ZNI-S/R4GC8 - RJ45 coupling

1041760

<https://www.phoenixcontact.com/in/products/1041760>



RJ45 coupling, degree of protection: IP20, number of positions: 8, 10 Gbps, CAT6_A, material: Metal, connection method: Coupling, cable outlet: straight, Adapter-free design, Ethernet

NBC-PP-J1PGY-S/R4GC8 - DIN rail adapter



1769127

<https://www.phoenixcontact.com/in/products/1769127>

Technical data

Product properties

Product type	Patch panel
Type	RJ45
Number of positions	8
Number of slots	1

Electrical properties

Frequency range	500 MHz
Transmission medium	Copper

Material specifications

Flammability rating according to UL 94	V0
--	----

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
----------------------	------

NBC-PP-J1PGY-S/R4GC8 - DIN rail adapter



1769127

<https://www.phoenixcontact.com/in/products/1769127>

Classifications

ECLASS

ECLASS-13.0	19170112
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

NBC-PP-J1PGY-S/R4GC8 - DIN rail adapter

1769127

<https://www.phoenixcontact.com/in/products/1769127>



Accessories

NBC-PP-P1PGY:10 - Dust protection cover

1041860

<https://www.phoenixcontact.com/in/products/1041860>

Dust protection cover



NBC-PP-F1PWH:10 - Plug Guard Security Frame

1041881

<https://www.phoenixcontact.com/in/products/1041881>

Plug Guard Security Frame



NBC-PP-J1PGY-S/R4GC8 - DIN rail adapter

1769127

<https://www.phoenixcontact.com/in/products/1769127>



NBC-PP-A1PRD:10 - Port Guard Security Element

1041900

<https://www.phoenixcontact.com/in/products/1041900>



Port Guard Security Element

UC-TMF 16 - Marker for terminal blocks

0819262

<https://www.phoenixcontact.com/in/products/0819262>



Marker for terminal blocks, Sheet, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, BLUEMARK E.CARD, mounting type: latching, for terminal block width: 16 mm, Number of individual labels: 32, text field height: 5.1 mm, text field width: 15.45 mm

NBC-PP-J1PGY-S/R4GC8 - DIN rail adapter

1769127

<https://www.phoenixcontact.com/in/products/1769127>



UC-TMF 16 CUS - Marker for terminal blocks

0824678

<https://www.phoenixcontact.com/in/products/0824678>



Marker for terminal blocks, can be ordered: by sheet, white, labeled according to customer specifications, mounting type: snap into flat marker groove, for terminal block width: 16 mm, Number of individual labels: 32, text field height: 5.1 mm, text field width: 15.45 mm

FL DIN RA - DIN rail adapter

2891053

<https://www.phoenixcontact.com/in/products/2891053>



The FL DIN RA is installed in a standard, 19-inch rack (EIA-310-D, IEC 60297-3-100) to allow DIN rail mounted equipment to be rack mounted.

NBC-PP-J1PGY-S/R4GC8 - DIN rail adapter




1769127

<https://www.phoenixcontact.com/in/products/1769127>

UC-TMF 16 VT - Marker for terminal blocks

0822699

<https://www.phoenixcontact.com/in/products/0822699>



Marker for terminal blocks, Sheet, violet, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: snap in, for terminal block width: 16 mm, Number of individual labels: 32

UC-TMF 16 YE - Marker for terminal blocks

0819259

<https://www.phoenixcontact.com/in/products/0819259>



Marker for terminal blocks, Sheet, yellow, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, BLUEMARK E.CARD, mounting type: latching, for terminal block width: 16 mm, Number of individual labels: 32, text field height: 5.1 mm, text field width: 15.45 mm

NBC-PP-J1PGY-S/R4GC8 - DIN rail adapter



1769127

<https://www.phoenixcontact.com/in/products/1769127>

UC-TMF 16 RD CUS - Marker for terminal blocks

0824682

<https://www.phoenixcontact.com/in/products/0824682>



Marker for terminal blocks, can be ordered: by sheet, red, labeled according to customer specifications, mounting type: snap into flat marker groove, for terminal block width: 16 mm, Number of individual labels: 32, text field height: 5.1 mm, text field width: 15.45 mm

UC-TMF 16 GN - Marker for terminal blocks

0817921

<https://www.phoenixcontact.com/in/products/0817921>



Marker for terminal blocks, Sheet, green, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: latching, for terminal block width: 16 mm, Number of individual labels: 32, text field height: 5.1 mm, text field width: 15.45 mm

NBC-PP-J1PGY-S/R4GC8 - DIN rail adapter



1769127

<https://www.phoenixcontact.com/in/products/1769127>

UC-TMF 16 BU CUS - Marker for terminal blocks

0824679

<https://www.phoenixcontact.com/in/products/0824679>



Marker for terminal blocks, can be ordered: by sheet, blue, labeled according to customer specifications, mounting type: snap into flat marker groove, for terminal block width: 16 mm, Number of individual labels: 32, text field height: 5.1 mm, text field width: 15.45 mm

UC-TMF 16 OG - Marker for terminal blocks

0817811

<https://www.phoenixcontact.com/in/products/0817811>



Marker for terminal blocks, Sheet, orange, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: latching, for terminal block width: 16 mm, Number of individual labels: 32, text field height: 5.1 mm, text field width: 15.45 mm

NBC-PP-J1PGY-S/R4GC8 - DIN rail adapter



1769127

<https://www.phoenixcontact.com/in/products/1769127>

UC-TMF 16 OG CUS - Marker for terminal blocks

0824681

<https://www.phoenixcontact.com/in/products/0824681>




Marker for terminal blocks, can be ordered: by sheet, orange, labeled according to customer specifications, mounting type: snap into flat marker groove, for terminal block width: 16 mm, Number of individual labels: 32, text field height: 5.1 mm, text field width: 15.45 mm

UC-TMF 16 VT CUS - Marker for terminal blocks

0824683

<https://www.phoenixcontact.com/in/products/0824683>



Marker for terminal blocks, can be ordered: by sheet, violet, labeled according to customer specifications, mounting type: snap into flat marker groove, for terminal block width: 16 mm, Number of individual labels: 32

NBC-PP-J1PGY-S/R4GC8 - DIN rail adapter



1769127

<https://www.phoenixcontact.com/in/products/1769127>

UC-TMF 16 BU - Marker for terminal blocks

0817905

<https://www.phoenixcontact.com/in/products/0817905>



Marker for terminal blocks, Sheet, blue, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: latching, for terminal block width: 16 mm, Number of individual labels: 32, text field height: 5.1 mm, text field width: 15.45 mm

UC-TMF 16 YE CUS - Marker for terminal blocks

0824684

<https://www.phoenixcontact.com/in/products/0824684>



Marker for terminal blocks, can be ordered: by sheet, yellow, labeled according to customer specifications, mounting type: snap into flat marker groove, for terminal block width: 16 mm, Number of individual labels: 32, text field height: 5.1 mm, text field width: 15.45 mm

NBC-PP-J1PGY-S/R4GC8 - DIN rail adapter



1769127

<https://www.phoenixcontact.com/in/products/1769127>

UC-TMF 16 GN CUS - Marker for terminal blocks

0824680

<https://www.phoenixcontact.com/in/products/0824680>



Marker for terminal blocks, can be ordered: by sheet, green, labeled according to customer specifications, mounting type: snap into flat marker groove, for terminal block width: 16 mm, Number of individual labels: 32, text field height: 5.1 mm, text field width: 15.45 mm

UC-TMF 16 RD - Marker for terminal blocks

0817824

<https://www.phoenixcontact.com/in/products/0817824>



Marker for terminal blocks, Sheet, red, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, BLUEMARK E.CARD, mounting type: latching, for terminal block width: 16 mm, Number of individual labels: 32, text field height: 5.1 mm, text field width: 15.45 mm

NBC-PP-J1PGY-S/R4GC8 - DIN rail adapter



1769127

<https://www.phoenixcontact.com/in/products/1769127>

CUC-I-D1ZNI-S/R4GC8 - RJ45 coupling

1041760

<https://www.phoenixcontact.com/in/products/1041760>



RJ45 coupling, degree of protection: IP20, number of positions: 8, 10 Gbps, CAT6_A, material: Metal, connection method: Coupling, cable outlet: straight, Adapter-free design, Ethernet

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in