

FST-21.25A-4

✓ ACTIVE

TE Internal #: 7-1437184-1

Wire-to-Board, 4 Position, 2.54 mm [.1 in] Centerline, 31.75 mm [1.25 in] Length, Printed Circuit Board, Wire-to-Board Jumpers & Shunts

[View on TE.com >](#)



Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Jumpers & Shunts



Connector System: **Wire-to-Board**

Number of Positions: **4**

Centerline (Pitch): **2.54 mm [.1 in]**

Product Length: **31.75 mm [1.25 in]**

Connector & Contact Terminates To: **Printed Circuit Board**

Features

Product Type Features

Connector System	Wire-to-Board
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Conductors	4
Number of Rows	1
Number of Positions	4

Electrical Characteristics

Operating Voltage	300 VAC
-------------------	---------

Body Features

Jumper Insulation Material	PTFE
----------------------------	------

Contact Features

Pin Arrangement (Right)	A
Pin Arrangement (Left)	A
Contact Current Rating (Max)	3 A



Housing Features

Centerline (Pitch)	2.54 mm[.1 in]
--------------------	----------------

Dimensions

Wire Size	24 AWG
Product Length	31.75 mm[1.25 in]

Usage Conditions

Operating Temperature Range	-40 – 150 °C[-40 – 302 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

FST-21.25A-4


Wire-to-Board, 4 Position, 2.54 mm [.1 in] Centerline, 31.75 mm [1.25 in] Length, Printed Circuit Board, Wire-to-Board Jumpers & Shunts






TE Part # 5-1437184-7

[FST-21.1A-10](#)



TE Part # 7-1437184-4

[FST-21.25B-12](#)



TE Part # 6-1437184-3

[FST-21.25A-10](#)

Customers Also Bought



TE Part #CAT-D48-ST273

[DEUTSCH Solid Contacts](#)



TE Part #DT04-2P

[REC, 2P, GRY, N](#)



TE Part #DT06-2S

[PLG, 2P, GRY, N](#)



TE Part #CAT-D487-W416

[Wedgelocks: DEUTSCH DT](#)




TE Part #114017-ZZ

[SEALING PLUG, SIZE 12/16, WHT](#)



TE Part #CAT-AM71-CH8172

[AMP SUPERSEAL 1.5MM, CONNECTOR HOUSING](#)



TE Part #281934-2

[SINGLE WIRE SEAL](#)

Documents

Product Drawings

[FST-21.25A-4](#)

English

Product Specifications

[Product Specification](#)

English

Agency Approvals

[UL Report](#)

English