



TE Internal #: 2-5331272-3
3.51 mm [.138 in] Socket Length, 1.32 mm [.052 in] PCB Hole,
Closed Bottom, .162 mm² Wire, 25 AWG, Cable-to-Board, Power &
Signal, Pin Sockets
[View on TE.com >](#)

Connectors > Socket Connectors > Pin Sockets > Miniature Spring Sockets: Closed Bottom, Beryllium Copper, 4A



Socket Length: 3.51 mm [.138 in]
PCB Hole Diameter: 1.32 mm [.052 in]
Socket Sleeve Style: Closed Bottom
Wire Size: 25 AWG

[All Miniature Spring Sockets: Closed Bottom, Beryllium Copper, 4A \(13\)](#)

Features

Product Type Features

Connector & Contact Terminates To	Printed Circuit Board
Socket Sleeve Style	Closed Bottom
Connector System	Cable-to-Board
Sealable	No

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Body Features

Sleeve Plating Material	Tin
Sleeve Material	Copper

Contact Features

Contact Spring Plating Material	Gold
Contact Base Material	Beryllium Copper
Contact Mating Area Plating Material Thickness	30 µm[30 µin]
Contact Spring Plating Thickness	.762 µm[30 µin]



Contact Current Rating (Max)	4 A
------------------------------	-----

Termination Features

Termination Method to PCB	Through Hole - Press-Fit
Termination Method to Wire & Cable	Solder
Insertion Method	Hand/Semi-Automatic

Dimensions

PCB Thickness (Recommended)	.79 – 3.18 mm [.031 – .125 in]
Socket Length	3.51 mm [.138 in]
PCB Hole Diameter	1.32 mm [.052 in]
Wire Size	25 AWG
Mating Pin Diameter Range	.46 – .51 mm [.018 – .02 in]

Usage Conditions

Operating Temperature Range	-65 – 125 °C [-85 – 257 °F]
-----------------------------	-----------------------------

Operation/Application

Solder Process Feature	None
Circuit Application	Power & Signal

Packaging Features

Packaging Method	Bag, Loose Piece
Packaging Quantity	2000

Other

Spring Material	Beryllium Copper
-----------------	------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC



Free

Solder Process Capability

Pin-in-Paste capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2-5331272-7
SOCKET,MIN-SPR SN-AU SER-2

Customers Also Bought



TE Part #214355-E
MSPEED 133 M SMD M1 * A-G VVV 137 176 *



TE Part #292172-2
CT POST HDR ASSY 2P IN-TUBE BL



TE Part #5084614-4
0.8FH,P05H.5,100,30/Sn,TU



TE Part #5-2176363-0
RQ 0402 1K4 0.1% 10PPM 5K RL



TE Part #6339082-3
LED STK MJ ASSY,2X4,8 POS,CAT5




TE Part #282036-012
44A0111-22-6



TE Part #282037-000
44A0111-22-7



TE Part #2820123007
44A0111-18-2



Documents

Product Drawings

[SOCKET,MIN-SPR SN-AU SER-2](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_2-5331272-3_O.2d_dxf.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_2-5331272-3_O.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-5331272-3_O.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Product Specification](#)

English