



Description

The new generation Palm Size Multimeters redefines the performance standards for entry-level digital multimeters. These models ensure that users can work safely in CAT II 250V environment.

Features

- Clear LCD Display
- Equipped with Comfortable Protective Cover, Test Probe Holder
- 2 Meters Drop Test, Precision Protection
- Auto Power Off
- Auto Backlight Off
- Loud Buzzer Sound
- Knobs Shift Smoothly, In-line with Ergonomics
- ETL certified

Specification Table

Characteristics	72-13430	72-13435	72-13440
Max Display	1999		
Range Selection	Auto	Manual	
Diode Test	✓		
Continuity Buzzer	✓		
Overload Alarm	✓		
Data Hold	✓		
Relative Mode	✓	-	
Low Battery Indication	✓		
NCV	-	-	✓
DC Voltage	200mV/2V/20V/200V/250V, ±(0.8%+1)	200mV/2000mV/20V/200V/250V, ±(0.5%+2)	200mV/2000mV/20V/200V/250V, ±(0.5%+2)
AC Voltage	200mV/2V/20V/200V/250V, ±(1% +2)	200V/250V, ± (1.2%+3)	200V/250V, ±(1.2%+10)
AC Current	200µA/2000µA/20mA/ 200mA/2A/10A, ±(1.2%+3)	-	-
DC Current	200µA/2000µA/20mA/ 200mA/2A/10A, ±(1%+3)	2000µA/20mA/ 200mA/10A, ±(1%+3)	2000µA/20mA/ 200mA/10A, ±(1%+3)
Capacitance	2nF/20nF/200nF/2uF/ 20uF/200uF, ±(3%+5)	-	-

www.element14.com

www.farnell.com
www.newark.com
www.cpc.co.uk

Palm Size Digital Multimeter

multicompPRO

Characteristics	72-13430	72-13435	72-13440
Resistance	200Ω/2kΩ/20kΩ/200kΩ/ 2MΩ/20MΩ/200MΩ, ±(0.8%+2)	200Ω/2kΩ/20kΩ/200kΩ/20MΩ, ±(0.8%+2)	200Ω/2kΩ/20kΩ/200kΩ/ 2MΩ/20MΩ/200MΩ, ±(0.8%+2)
Temperature	-	-40°C to 1000°C	-
	-	-40°F to 1832°F	-
Power	AAA 1.5V x 2		
Standard Accessories	Type K Thermocouple (Part Number 72-13435 only), English Manual, Test Leads, Protective Case		
Product Weight	206g (Battery Included)		
Product Size	134mm x 77mm x 47mm		

Part Number Table

Description	Part Number
DMM, Handheld, Auto/Manual, 2000 Count	72-13430
DMM, Handheld, Manual, 2000 Count	72-13435
DMM, Handheld, Manual, 2000 Count	72-13440

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Tenma is the registered trademark of the Group. © Premier Farnell Limited 2016.

www.element14.com

www.farnell.com

www.newark.com

www.cpc.co.uk

multicompPRO