




TE Internal #: 2480662-1
SMA Pigtail Cable Assembly, .05 m [.164 ft], 20 GHz Operating
Frequency, 50 ohm, 26 AWG, 1.19 mm [.047 in] Diameter, SMA Jack
End A
[View on TE.com >](#)

Cable Assemblies > RF Cable Assemblies



Cable Assembly Type: **SMA Pigtail**
Cable Assembly Length: **.05 m [.164 ft]**
Operating Frequency: **20 GHz**
Impedance: **50 Ω**
Wire Size: **26 AWG**

Features

Contact Features

Contact Underplating Material	Nickel
Contact Mating Area Plating Material	Gold
Contact Base Material	Beryllium Copper
Center Contact Plating	Gold

Body Features

Body Plating Material	Gold
Conductor Material	Brass
Shield Plating Material	Nickel
Conductor Plating Material	Gold
Shield Material	Brass

Operation/Application

Shielded	Yes
Operating Frequency	20 GHz

Product Type Features

--	--



Cable Assembly Type	SMA Pigtail
Cable Assembly (End A)	SMA Jack
Coax Cable Type	.047 Semi Rigid

Other

Cable Assembly Length	.05 m[.164 ft]
EU RoHS Compliance	Compliant with Exemptions

Electrical Characteristics

Impedance	50 Ω
-----------	------

Dimensions

Wire Size	26 AWG
Outside Cable Diameter	1.19 mm[.047 in]

Usage Conditions

Operating Temperature Range	-50 – 105 °C[-58 – 221 °F]
-----------------------------	----------------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (4.75% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability










Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked.Additionally, the part



numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts

 <p>TE Part # L9000274-01 SMA Plug 50 Ohm .031 PCB Edge Mount</p>	 <p>TE Part # L9000273-01 SMA Plug 50 Ohm .031 PCB Edge Mount</p>	 <p>TE Part # 2466282-1 SMA PLUG STR SOLDER .085 .086 18 GHZ SUS</p>	 <p>TE Part # CONSMA007-G SMA Plug 50 Ohm Cable Crimp</p>
 <p>TE Part # CONSMA007-R178 SMA Plug 50 Ohm Cable Crimp</p>	 <p>TE Part # CONSMA012 SMA RA Plug 50 Ohm Cable Crimp</p>	 <p>TE Part # CONSMA007-R58 SMA Plug 50 Ohm Cable Crimp</p>	 <p>TE Part # L9000276-01 SMA Plug 50 Ohm .062 PCB Edge Mount</p>
 <p>TE Part # L9000275-01 SMA Plug 50 Ohm .062 PCB Edge Mount</p>	 <p>TE Part # CONSMA007 SMA Plug 50 Ohm Cable Crimp</p>		

Documents

Product Drawings

SMA F St BHD to Open Semi-rigid.047 50mm

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2480662-1_1.3d_igs.zip

2480662-1

SMA Pigtail Cable Assembly, .05 m [.164 ft], 20 GHz Operating Frequency, 50 ohm, 26 AWG, 1.19 mm [.047 in] Diameter, SMA Jack End A



English

Customer View Model

[ENG_CVM_CVM_2480662-1_1.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2480662-1_1.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[dnd-fly-RF-cable-assemblies-product-expansion](#)

English