

M12 Connector

TE Internal #: T4111001041-000

Cable-to-Cable, 4 Position, Sealable, Wire & Cable, Signal, Cable Mount (Free-Hanging), Reverse Gender, M12 Connector, Standard Circular Connectors

[View on TE.com >](#)



Connectors > Circular Connectors > Standard Circular Connectors



Connector System: **Cable-to-Cable**
Number of Positions: **4**
Sealable: **Yes**
Connector & Contact Terminates To: **Wire & Cable**
Contact Current Rating (Max): **4 A**

Features

Electrical Characteristics

Operating Voltage	250 VDC
-------------------	---------

Packaging Features

Packaging Quantity	1
--------------------	---

Industry Standards

UL Flammability Rating	UL 94HB
------------------------	---------

Termination Features

Termination Method to Wire & Cable	Screw Terminal
------------------------------------	----------------

Other

Field Serviceable	Yes
EU RoHS Compliance	Compliant with Exemptions
EU ELV Compliance	Compliant with Exemptions

Usage Conditions

IP Dust Sealing Level	6
-----------------------	---



IP Water Sealing Level	IP67
Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]

Body Features

O-Ring Material	Silicone
Environmental Protection	IP67
Environmental Protection Type	Elastomer Sealed
Primary Product Color	Black
Peripheral Seal Material	Silicone
Feedthrough Type	Yes
Shell Plating Material	Unplated
Shell Base Material	Plastic
Circular Connector Insulation Material Type	Polyamide 66 GF25
Hermetically Sealed	Yes

Mechanical Attachment

Mating Retention Type	Threaded Coupling
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)
Polarization Code	A
Mating Alignment Type	Keyed

Operation/Application

Durability Rating	100 Cycles
Circuit Application	Signal
Shielded	No

Configuration Features

Keying & Polarized Position Locations	A
Factory Installed Backshell	No
Number of Positions	4
Number of Power Positions	0
Number of Signal Positions	4
Contacts Preloaded	Yes

Product Type Features

Assembly Requirement	Factory Assembled
----------------------	-------------------



Circular Connector Shell Type	All Plastic
Connector Product Type	Connector Assembly
Assembly Type	Electrical Connector
Connector System	Cable-to-Cable
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Circular Connector Type	Plug
Shell Type	Plastic

Contact Features

Contact Current Rating (Max)	4 A
Reverse Gender	Yes
Circular Connector Contact Type	Pin

Housing Features

Circular Connector Shell Size	20
-------------------------------	----

Dimensions

Wire Size	18 – 24 AWG
-----------	-------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (3.7% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

















Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as





EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




 TE Part # 1838275-2 M12 Fld Ser CONN. Male Pin Sld	 TE Part # T4141012041-001 M12,REAR MOUNTING,FEMALE,A CODE,4P	 TE Part # T4171310004-801 M12,FRONT MOUNT,F,A,4P,WITH FERRULE,0.2M	 TE Part # 2075001-4 M12 MtI FEMALE PNL CONN. PCB Front
 TE Part # T4141016041-000 M12,REAR MOUNT,FEMALE,A,4P, M16,POTTING	 TE Part # 2273054-1 M12 Female pnl Mld Rear Mt PG9 pigt A	 TE Part # T4171110004-802 M12,REAR MOUNT,FEMALE,A,4P,0.5 M WIRE	 TE Part # T4131012041-001 M12,REAR MOUNT,FEMALE,A,4P, SOLDER WIRE
 TE Part # CAT-C73765-M1F M12 Panel Mount Wire	 TE Part # CAT-C73765-M1H M12 Panel Mount PCB	 TE Part # T4110001041-000 M12,FEMALE,STRAIGHT,A CODE,4P, PG7,GOLD	 TE Part # T4141012041-003 M12,REAR MOUNT,FEMALE,A,4P, SOLDER PCB
 TE Part # T4171110004-004 M12,REAR MOUNTING,FEMALE,A,4P, 1.5M WIRE	 TE Part # CAT-C73765-M1G M12 Panel Mount Solder Cups	 TE Part # T4151480014-002 RPC-M12-FR-4CON-PUR-BK0.5-1.0	 TE Part # T4171110004-801 M12,REAR MOUNT,FEMALE,A,4P,0.2 M WIRE



Also in the Series | **M12 Connector**



Customers Also Bought



Documents

Product Drawings
[RPC-M12-MS-4CON-PG7-MU](#)

English

CAD Files
Customer View Model
[ENG_CVM_CVM_T4111001041-000_B.3d_igs.zip](#)



English

Customer View Model

[ENG_CVM_CVM_T4111001041-000_B.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_T4111001041-000_B.2d_dxf.zip](#)

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[M8 / M12 Connector System Catalog](#)

English

Product Specifications

[Application Specification](#)

English

Agency Approvals

[UL](#)

English