



WTPP MS SET

NANO/PICO SOLDERING IRON WTPP MS WITH SAFETY REST (STOP & GO),

40 W, 12 V

ORDER NO: T0052924299

COMPACT. POWERFUL.VERSATILE. BOOST YOUR PRODUCTIVITY

As production in the electronics, medical technology and aerospace industries

is getting faster and faster as components get smaller and smaller. The increasing use of small SMDs has led to a growing demand for nano soldering tips to meet these precision requirements.

Weller RT Nano/Pico: Ideal for soldering ultra-small SMDs from 0402 to 01005. Perfect for working on tiny components and pads with moderate power requirements. MIL-SPEC and IPC standard tips (MS versions) are available to ensure potential free soldering. For the electronics, aerospace, medical, sensor, military and automotive industries.



NANO/PICO SOLDERING IRON 40 W, 12 V Set including tip and Safety Rest	SCOPE OF SUPPLY
RTPTIP FAMILY	WTPP MS Nano Soldering Iron, 40 W, 12 V RTP 004 S MS Nano Soldering Tip WSR 205 Safety Rest with Stop & Go Function
ILITARY STANDARD	
FOR EXTREMELY SMALL COMPONENTS	TECHNICAL DATA SOLDERING IRON WTPP MS
vith high energy demand	Temperature range °C 100 - 450 Temperature range °F 150 - 950
FOR MINIATURE WORKS Inder a microscope	Power consumption 40 W (55 W)
RT SOLDERING TIPS can be exchanged quickly and easily	Mains supply voltage (V/Hz) 12V/AC
CTIVE TIP (CARTRIDGE)-SYSTEM	Heat-up time (50°C to 350°C) (120°F to 660°F) 3 sec.
lows exchange of soldering tip despite a hot soldering iron	Safety rest
EXTREMELY SHORT HEATING TIME 3 sec.	WSR 205 Tip type series
	RTP MS
TANDBY FUNCTION	Supply unit WT 1M, WT 2M, WR 3M
ESD-SAFE	Subject to technical alterations and amendments.

#PowerfulTogether

