




Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal Type: **Receptacle**

Connector & Housing Type: **Receptacle**

Number of Positions: **1**

Terminal Orientation: **Straight**

UL Flammability Rating: **UL 94V-2**

Features

Product Type Features

Sealable	No
Connector & Housing Type	Receptacle

Configuration Features

Number of Positions	1
---------------------	---

Body Features

Primary Product Color	Red
-----------------------	-----

Contact Features

Terminal Type	Receptacle
Terminal Orientation	Straight
Contact Mating Retention	Without

Mechanical Attachment

Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

--	--



Housing Material	Polyamide
------------------	-----------

Dimensions

Product Length	24.4 mm[.961 in]
----------------	------------------

Industry Standards

UL Flammability Rating	UL 94V-2
------------------------	----------

Packaging Features

Packaging Quantity	20000
--------------------	-------

Product Compliance


For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2238143-1
250 FASTON,REC.,22-18 AWG,NPST




TE Part # 1742198-1
250 FASTON,REC.,18-14 AWG,NPST



TE Part # 444335-1
250 FASTON REC 16-14 AWG BR



TE Part # 2238173-3
250 FASTON,REC.,22-12 AWG,TPBR



TE Part # 2238196-3
FASTON 250 STD REC STR 18-14TPBR




TE Part # 2238204-3
FASTON 250 STD REC STR 22-18TPBR

Also in the Series | FASTON 250




Compression Connectors(4)



Crimp Terminal Housings(116)



Insulation Boots & Sleeves(16)



Magnet Wire Terminals(1)



PCB Terminals(133)



Quick Disconnects(421)




Splices(4)

Customers Also Bought



TE Part #794742-1
12P UMNL PLUG HSG NATL



TE Part #C55984-000
HX-SCE-9.5-50-S1-4




TE Part #1-1969443-2
EP 2.5 TPA Retainer, 12 Pos




TE Part #1-282047-1
AMP MONO-SHAPE P.C.B.CONN7P. GL





TE Part #1969106-2
ULTRA-POD 187 ASSY REC 22-16
AWG TPBR



TE Part #1-520987-4
250 FASTON HSG.,REC.,4 POS,BLACK



TE Part #1-880488-2
FASTON 187 HOUSING RECEPTACLE



TE Part #63482-4
RING 18-14 110-145 10 025TPSTL

TE Part #EM5032-000
ZHD-SCE-5K-3.2-50-SS3-9



TE Part #61795-9
RING 18-14 105-145 #10 025TPST

Documents

Product Drawings

250 FASTON INS POST.,REC.,1 POS,RED

English

CAD Files

Customer View Model

ENG_CVM_CVM_1-735075-1_AW.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-735075-1_AW.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-735075-1_AW.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

6,35 FASTON RECPTACLES AND TAB SLEEVES

English

Product Specification

English

Agency Approvals

UL Report

English

