



Antennas



Antenna Type: **Panel**  
Band Type: **Triple Band**  
Primary Application: **Wi-Fi**  
Wireless Application: **Wi-Fi**  
Mounting Location: **External**

Features

Usage Conditions

Cable Type	RG 58
------------	-------

Body Features

Product Weight	540 g[19.05 oz]
----------------	-----------------

Dimensions

Product Width	200 mm[7.87 in]
Product Length	200 mm[7.87 in]
Product Height	46.5 mm[1.83 in]
Cable Length	.75 m[2.46 ft]
Cable Insulation Diameter (Max)	2.8 mm[.11 in]

Product Availability

Applicable Region	Global
-------------------	--------

Electrical Characteristics

Impedance	50 Ω
Antenna Operation	Passive
VSWR (Max)	< 2.0:1

Packaging Features

Packaging Method	Box
------------------	-----



Other

Precision Level	Standard
EU RoHS Compliance	Compliant with Exemptions
EU ELV Compliance	Compliant with Exemptions

Signal Characteristics

Frequency Band	4900 – 5900 MHz, 2400 – 2500 MHz, 6000 – 7125 MHz
Gain (Max)	9.6 dB
Frequency Category	2400 – 7125
Peak Gain	> 6 dBi

Operation/Application

Antenna Environment	Outdoor
Wireless Standard	802.11 a/g/n/ac/ax/be Wifi
Directionality	Directional

Mechanical Attachment

Polarization	Dual Slant 45°
Mounting Type	Pole/Mast/Bracket Mount

Industry Standards

IP Rating	IP67
Primary Application	Wi-Fi
Wireless Application	Wi-Fi

Configuration Features

Antenna Style	Panel
Antenna Type	Panel
Band Type	Triple Band
Mounting Location	External
Port Configuration	Multiple Ports

Product Type Features

Antenna Termination	RP-SMA
Antenna Product Type	Antenna

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)




EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (3.34% in Component Part) <b>Article Safe Usage Statements:</b> Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts

 <p>TE Part # PSQ24495-91RSM Panel,Dband,91,RSMAM 2.4 - 6.0,5dBi,</p>	 <p>TE Part # PSQ24495-91NF Panel,Dband,91CM,NF 2.4-6.0,5dBi,</p>	 <p>TE Part # L000962-01 PANEL,TBAND,75CM, RP-SMAM, 2PORTS</p>	 <p>TE Part # PSQ24495-91NM Panel,Dband,91CM,NM 2.4-6.0,5dBi,</p>
--	--	---	--



Documents

Product Drawings

PANEL,TBAND,75CM, RP-SMAM, 4PORTS

English

Datasheets & Catalog Pages

ANT-DS-ProSig-L000962

English

Product Specifications

Product Specification

English