




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **.75 – 2.5 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Product Type Features

Insertion Force	Normal
-----------------	--------

Electrical Characteristics

Voltage Rating	300 V
----------------	-------

Body Features

Insulation Material	Nylon
---------------------	-------

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Tin
Crimp Type	Compression Crimp
Barrel Type	Closed

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------



Mating Retention TypeDimple

Dimensions

Product Length	21.6 mm[.85 in]
Compatible Insulation Diameter Range	3.3 mm[.13 in]
Wire Size	.75 – 2.5 mm²

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Packaging Features

Packaging Method	Bag
------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought





TE Part #6-1579022-8
ERGOCRIMP DIE SET, PQ- 6,0 SQ.MM



TE Part #4-1377175-7
SMP 0-0180900-0



TE Part #4-1377175-0
SMP 0-0180901-0



TE Part #3-1377175-7
SMP 0-0180923-0



TE Part #3-1377175-9
SMP 0-0180941-0

TE Part #8-1372723-1
cutting plate

TE Part #6-1372721-9
CUTTING PLATE

TE Part #1372214-9
GROOVE NUT

TE Part #1-1372477-0
CUTTER



TE Part #374592-E
SRCP 2,54 5 M 1 SMD 137 E1 094 *
GURT *

Documents

Product Drawings

SMP 0-0042241-2

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-1377175-4_G1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_3-1377175-4_G1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-1377175-4_G1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications



Application Specification

English