



Part Number : [191600071](#)  
Product Description : Closed-End Insulated  
Splice for 22-12 AWG Wire, Tape and Reel  
Series Number : 19160  
Status : Active  
Product Category : Splices  
Engineering Number : NC-2212T




Documents & Resources

Drawings  
[191600071\\_sd.pdf](#)

Specifications  
[PK-19408-109-001.pdf](#)  
[PS-19902-015-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

- Multiple Part Product Compliance Statements
- Eu RoHS
  - REACH SVHC
  - Low-Halogen

- Multiple Part Industry Compliance Documents
- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

---

### Part Details

#### General

Status	Active
Category	Splices
Series	19160
Description	Closed-End Insulated Splice for 22-12 AWG Wire, Tape and Reel
Product Name	Closed-End Insulated
UPC	800753110786

#### Agency

CSA	LR18689
UL	E32244

#### Electrical

Voltage - Maximum	600V
-------------------	------

#### Physical

Barrel Type	Closed
Color - Resin	Natural
Flammability	94V-2
Insulation	Nylon (PA)
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.687/g
Packaging Type	Adhesive Tape on Reel
Temperature Range - Operating	105°C
Wire Insulation Diameter	6.86mm max.

Wire Size (AWG)	12, 14, 16, 18, 20, 22
-----------------	------------------------

---

Application Tooling

Global

Description	Part Number
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	<u>192880239</u>
Mini-Mac Applicator	<u>638853500</u>