




Connectors > Automotive Connectors > Automotive Connector Accessories > Automotive Connector Caps & Covers



Number of Positions: 32  
Primary Product Color: Gray  
Protection & Strain Relief Accessory Type: Cover Assembly  
Primary Product Material: PBT GF  
Strain Relief: With

Features

Product Type Features

|                                           |                |
|-------------------------------------------|----------------|
| Protection & Strain Relief Accessory Type | Cover Assembly |
|-------------------------------------------|----------------|

Configuration Features

|                                |    |
|--------------------------------|----|
| Compatible With Connector Code | A  |
| Number of Positions            | 32 |

Body Features

|                          |        |
|--------------------------|--------|
| Primary Product Color    | Gray   |
| Primary Product Material | PBT GF |

Mechanical Attachment

|               |      |
|---------------|------|
| Strain Relief | With |
|---------------|------|

Usage Conditions

|                             |                           |
|-----------------------------|---------------------------|
| Operating Temperature (Max) | 85 °C[185 °F]             |
| Operating Temperature Range | -40 – 85 °C[-40 – 185 °F] |

Packaging Features

|                    |        |
|--------------------|--------|
| Packaging Method   | Carton |
| Packaging Quantity | 500    |

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)




|                                               |                                                                                                                                 |
|-----------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                       |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                       |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                         |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2024 (241)<br>Candidate List Declared Against: JUNE 2024 (241)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                             |
| Solder Process Capability                     | Not applicable for solder process capability                                                                                    |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 968265-1  
32POS MQS REC



TE Part # CAT-SIGH262  
Signal Header




TE Part # 929052-1  
MQS ABDECKKAPPE 32P

Customers Also Bought



TE Part #1-2176503-7  
CJP 80W 12R 5% Lead



TE Part #953486-1  
32pos MQS .63 header 90deg



TE Part #5-963715-1  
MQS0,63 Sn rec LL unseal. 0,5-0,75



TE Part #1-776231-6  
35POS,PIN DIA 1.3,HDR ASSY, 180DEG,COD 6






TE Part #1-2141857-3  
AMP MCP 2.8, CONTACT




TE Part #TAD14745101-002  
M12D4-MS-MS-PUR TYPE C GREEN-1.0M



TE Part #1394522-1  
MIXED SOCKET HOUSING, 42POS. ,



TE Part #1571563-8  
FSM4JSMLTR=TACT SWITCH,SMT, T&R



TE Part #929051-1  
MQS ABDEKA M.HEB12P



TE Part #2436766-2  
60POS,HYBRID,TAB HSG ASSY,UNSLD

Documents

Product Drawings  
MQS ABDEKA M.HEB32P

English

CAD Files  
3D PDF

3D

Customer View Model  
ENG\_CVM\_CVM\_929053-1\_C.2d\_dxf.zip

English

Customer View Model  
ENG\_CVM\_CVM\_929053-1\_C.3d\_igs.zip

English

Customer View Model  
ENG\_CVM\_CVM\_929053-1\_C.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications  
Application Specification

English