



Connectors > Modular Jacks & Plugs > RJ Point Five Connectors > RJ Point Five Plug Kit: Single Plug



Port Configuration: **Multiple Ports**

Multiple Port Configuration: **Stacked**

Port Matrix Configuration: **2 x 1**

Modular Jacks & Plugs Products: **RJ point five**

Connector Contact Density: **High**

[All RJ Point Five Plug Kit: Single Plug \(4\)](#)

Features

Product Type Features

Connector System	Cable-to-Board
Modular Jacks & Plugs Products	RJ point five
Modular Connector Style	Jack
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	8
PCB Mount Orientation	Right Angle
Port Configuration	Multiple Ports
Multiple Port Configuration	Stacked
Port Matrix Configuration	2 x 1
Connector Contact Density	High
EMI Finger Location	Bottom, Sides, Top

Body Features

Modular Jack Latch Orientation	Inverted (Top) / Standard (Bottom)
--------------------------------	------------------------------------

Contact Features

Contact Current Rating (Max)	.02 A, .5 A, 1 A
------------------------------	------------------

Mechanical Attachment

Connector Mounting Type	Board Mount
-------------------------	-------------



Housing Features

Mating Entry Location	Side
Centerline (Pitch)	.9 mm[.035 in]

Operation/Application

Indicator Type	LED
Circuit Application	Signal
Shielded	Yes

Industry Standards

Performance Category	Cat 5e
----------------------	--------

Packaging Features

Packaging Method	Box & Tray, Tray
------------------	------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Customers Also Bought

TE Part #1-103638-1
12 MTE HDR SRST LATCH .100CL

TE Part #2318579-1
RCPT CONN R/A SMT 76 POSN QSFP-DD

TE Part #5179229-4
0.8FH,R05H.5,100,08/Sn,TU,SC

TE Part #1-1747981-2
Std HDMI, RA, SMT, Panel grd, Flange

TE Part #2170129-1
Recpt RJ.5 W/O MAG, 1X2 OFFSET

TE Part #2342933-1
QSFP-DD 1X1, STANDARD, W/ EXTRUDED HS

TE Part #9-1879253-5
RP 2B 22R1 0.1% 15PPM 1K RL

TE Part #1-1744037-0
10P EC PWR.200 CL HDR ASSY VRT

TE Part #1-2176311-7
RP 1E 0.1W 1K69 0.1% 25PPM 1K RL

TE Part #1052067-1
2037 5006 02,SMA RA CABLE PLUG

Documents

CAD Files

Customer View Model

ENG_CVM_CVM_2057131-1_A.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2057131-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2057131-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

RJ_POINT_FIVE_CONNECTOR_SYSTEM_QUICK_REF_GUIDE

English



Product Specifications

Product Specification

English