





Technical specification:




Technische Daten:

Dielectric withstanding voltage/ Spannungsfestigkeit:	1000 V, 50 Hz 1 min.
Current rating/ Strombelastbarkeit:	7,5 A (UL), 5 A (CSA,VDE)
Insulation resistance/ Isolationswiderstand:	$\geq 5 \text{ G}\Omega$
Temperature range/ Temperaturbereich:	- 55 °C ... + 125 °C
Solder cup accepts cable/ Lötkelch geeignet für Kabel:	max. AWG 20
Mating cycles/ Steckzyklen:	Quality class 3 = 50 Gütestufe 3

Materials/

Werkstoffe:

Contact/ Kontakt:	Cu alloy, Au over Ni
Insulator/ Isolierkörper:	PBT GF UL 94 V-0, green/grün
Shell/ Gehäuse:	Steel, Sn over Ni



Part no. / Part marked Art.-Nr. / Bedruckung:	Contact plating / Kontakt Veredelung:	dim. in mm D-SUB Combination Female 17W5S Solder cup D-SUB Combination Buchse 17W5S Lötkelch	
3017W5SAM99A10X	Signal contact Signalkontakt:		
	No contact on pos. A1 - A5 kein Kontakt an Pos. A1 - A5		
Index: a Original	Scale/ Maßstab: 2:1	dwg no / Z.-nr.: 13K1A5687	DIN-A3
Status: InBearbeitung			1 / 1
RoHS compliant/ konform			

CONEC