



Connectors > Rectangular Connectors > Standard Rectangular Connectors



Connector Product Type: **Housing**
Connector & Housing Type: **Plug**
Termination Method to Wire & Cable: **Crimp**
Connector System: **Wire-to-Wire**
Contact Retention Within Housing: **Without**

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Plug
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	6
Number of Rows	1

Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features

Multiple Contact Types	Without
Contact Layout	Inline
Contact Type	Socket



Contact Retention Within Housing	Without
----------------------------------	---------

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Panel Mount Feature	Without
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	Nylon
Centerline (Pitch)	6.35 mm[.25 in]

Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

Compatible With Agency/Standards Products	CSA, UL, VDE
UL Rating	Recognized
Compatible With Approved Standards Products	UL E28476
CSA Rating	Certified, LR 7189
Glow Wire Rating	Standard Part - Not Glow Wire
UL Flammability Rating	UL 94V-2

Packaging Features

Packaging Quantity	800
Packaging Method	Bag

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241)



Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Not applicable for solder process capability
---------------------------	--

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

 TE Part # 926301-1 8P UNIV.M-N-L.PLUG	 TE Part # 926300-3 6P UN-MNL STECKGEH	 TE Part # 926299-1 5P UNIV.M-N-L.PLUG	 TE Part # 1-480702-0 04P UMNL PLUG HSG NATL
 TE Part # 926299-3 5P UN-MNL STECKGEH	 TE Part # 926307-1 6P UNIV.M-N-L.CAP	 TE Part # 350779-1 04P UMNL PLUG HSG	 TE Part # 643253-1 06P UMNL ASSY MOD HSG VO
 TE Part # 1-480699-0 02P UMNL CAP HSG NATL	 TE Part # 926307-3 6P UN-MNL AUFN-GEH	 TE Part # 1863025-1 UNIVERSAL MNL 6-WAY CAP	 TE Part # 1-480764-0 05P UMNL CAP HSG NATL





TE Part # 926301-3
8P UN-MNL STECKGEH



TE Part # 1-1703061-2
PLUG, 2 CIRCUIT , UNIVERSAL MATE-N-LOK

Also in the Series | Universal MATE-N-LOK



Circular Power Connectors(2)



Connector Contacts(208)



Connector Hardware(12)



Power Contacts(208)



Rectangular Power Connectors(651)



Standard Circular Connectors(1)

Customers Also Bought



TE Part #926302-1
10& UNIV.M-N-L.PLUG



TE Part #926301-3
8P UN-MNL STECKGEH



TE Part #1903747-1
MINI UMNL GWT 2P PLUG HSG




TE Part #1SNA206394R0200
EV6I




TE Part #350570-3
UMNL SOK 24-18 PTPPHBZ



TE Part #HSA202N00420100000
723 HTEC PLUG, SPEEDTEC



TE Part #42770-2
250 FASTON FLAG TAB 18-14 AWG TPBR



TE Part #1-141708-2
MOD-4 REC.CONT.SCP.



TE Part #HSA202N00480100000
723 HTEC PLUG, SPEEDTEC



TE Part #ESA202N00320500000
915 PLUG

Documents

Product Drawings

6P UNIV.M-N-L.PLUG

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_926300-1_G.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_926300-1_G.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_926300-1_G.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Agency Approvals

UL

English