




Technical specification/




Technische Daten:

Working voltage/ Betriebsspannung:	60 V AC/DC
Insulation resistance/ Isolationswiderstand:	min. 3000 MOhm
Dielectric withstanding voltage/ Spannungsfestigkeit:	1000 V AC / minute
Operating temperature/ Betriebstemperatur:	- 55 °C ... + 105 °C
Current rating/ Strombelastbarkeit:	3 A
Contact Resistance/ Durchgangswiderstand:	max. 15 mOhm

Materials/

Werkstoffe:

Contact/ Kontakt:	Cu alloy, Underplate/ 50 µin Nickel Beschichtung:
	Contact area/ Kontaktbereich:
	Solder tails area/ Lötbereich:
Shell/ Gehäuse:	Steel, Nickel plated
Rivet, Boardlock/ Befestigungsniet:	Copper alloy
Insulator/ Isolierkörper:	Thermal plastic UL 94 V-0



Part no. / Part marked/
Art.-Nr. / Bedruckung:

301A10149X

				dim. in mm		D-SUB HD Male 44pos. solder cup stamped contact <i>D-SUB HD Stiftleiste 44pol. Lötke/ch gestanzte Kontakte</i>	
general tolerance/ <i>Allgemeintoleranz:</i>	0, ±0,5 ,0 ±0,3 ,00 ±0,2		Date/ <i>datum</i>	Name			
		drawn/ <i>gez.</i>	04.07.2022	Bub			
		appd./ <i>gepr.</i>	22.08.2022	Lehmenkühler			
Index: a Original	scale/ <i>Maßstab:</i> 2:1			dwg no / Z.-nr.:		16K1A3976	DIN- A3
RoHS compliant/ <i>konform</i>						1 / 1	

CONEC®