




used for: D-SUB

POS.	A ^{+0.2}	B ^{+0.2}	C	D ^{+0.25}	E ^{-0.30}	PART NO.
9	21.1	39.4	25.00 ^{+0.12 -0.13}	16.79	5.82	6STD09PAU99R40X
15	21.1	47.7	33.30 ^{+0.15 -0.1}	25.12	5.82	6STD15PAU99R40X
25	21.1	61.4	47.04 ^{±0.13}	38.84	5.69	6STD25PAU99R40X
37	21.1	77.9	63.50 ^{±0.13}	55.30	5.69	6STD37PAU99R40X



NOTES:

- METALSHELLS: COPPER ALLOY; min. 315µin TIN over 40-80µin NICKEL
- INSULATORS: PBT GF UL 94 V-0, BLACK
- CONTACTS: COPPER ALLOY
PLATING: 8µin HARD GOLD OVER min. 50µin NICKEL
- METAL BRACKET: ZINC DIE CAST; 30µin COPPER/40-120µin NICKEL/120-200µin TIN
- THREADED INSERT: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
- PCB-SNAP: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
PCB-HOLE: $\phi 3.1 \pm 0.1$; PCB THICKNESS 1.6mm
- HEXLOCKING SCREW: STAINLESS STEEL
- FRAME: ZINC DIE CAST; NICKEL PLATED
- P.C.B. HOLE DRILLINGS ON SHEET 2
- MAXIMUM TORQUE VALUE FOR THREAD: 6 in.LB
- CONNECTOR IS PART MARKED: PART-NO. CONEC ABC

Directive 2002/95 EC
"RoHS"
Compliant

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL
CUSTOMER APPROVAL DATE:
NAME: TITLE:
COMPANY NAME:
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL





THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY, WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name
a	Origin		

tolerance	dim. in mm
2006	date
drawn	31.07. Lehmenkühler
appd.	31.07. Kühle
norm	DIN 41652
d-old	

CONEC

scale: 2:1
material: SEE NOTES
title: D-SUB MALE 90° 9-37pos. SOLDER PIN ANGLED with threaded insert, metal bracket and clip
dwg no: AutoCAD 2006 DIN-A 18K2A307 3 sh:1/2
part no: SEE TABLE



APPROVAL # FREIGABE # DEBLOCKAGE # AUTOR/ZACION # APPROVAL	APPROVAL # FREIGABE # DEBLOCKAGE # AUTOR/ZACION # APPROVAL
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCKAGE # AUTOR/ZACION # APPROVAL	APPROVAL # FREIGABE # DEBLOCKAGE # AUTOR/ZACION # APPROVAL

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.

DRAWING BY HAND				tolerance		
				dim. in mm		
				2006	date	name
				drawn	31.07.	Lehmenkühler
				appd.	31.07.	Kühle
				norm	DIN 4 1652	
				d-old		
	a	Origin		CONEC®		
rev.	description	date	name			

scale:	2:1	
material:	SEE SHEET 1	
title:		
P.C.B. HOLE DRILLINGS D-SUB MALE 90° 9-37pos. ANGLED with threaded insert, metal bracket and clip		
dwg no:	AutoCAD 2006	DIN-A-
18K2A307		3
part no:		SEE SHEET 1