




Technical drawing of a stepped shaft. The shaft has three steps. The dimensions are indicated by arrows: 3 for the top step, 5 for the middle step, and 9,5 for the total length of the shaft.



Insert cavity/
Einsatznest: B, HEX 3,83 / .151"



				dim. in mm	Coaxial Plug Contact 90° 50 Ohm Inner conductor solder termination, outer conductor solder or crimp termination		
			Date/Datum	Name	Koaxial Stift Kontakt 90° 50 Ohm Innenleiter Lötanschluss, Aussenleiter Löt- oder Crimpanschluss		
		drawn/ gez.	19.06.2019	Lehmenkühler			
		appd./ gepr.	21.06.2019	Henneboel			
Index: a Original	scale/Maßstab: 5:1				dwg no / Z.-nr.:	13K1A5821	DIN- A4
Status: InBearbeitung							
RoHS compliant/konform							1 / 1