




STRIPPING DIMENSIONS



ASSEMBLY TOOLING:

1. CENTER CONTACT:
SOLDERED
2. OUTER CONDUCTOR:
SOLDERED OR CRIMPED
USE HANDCRIMP TOOL: 360X10519X
WITH TOOL INSERT: 360X11019X
INSERT CAVITY B: HEX 3.25/128

Part-No.	Finish Pos.1	Finish Pos.2	Finish Pos.3	Finish Pos.4 / 5
131A30029X	GOLD FLASH over NICKEL	GOLD FLASH over NICKEL	NICKEL PLATED	GOLD FLASH over NICKEL
131J30029X	min. 50µin HARD GOLD over min. 50µin NICKEL	min. 30µin HARD GOLD over min. 50µin NICKEL	NICKEL PLATED	GOLD FLASH over NICKEL

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND					tolerance unless otherwise specified: (b) x. ± 0.5 .x ± 0.35 .xx ± 0.25				scale: 10:1		
							dim. in mm		material: COPPER ALLOY (Pos. 1 - 5)		
						date	name		title: COAXIAL CONTACT PLUG 75 OHM for Cable 179B/U, 187A/U center contact solder, outer contact solder/crimp		
					drawn	09.12.09	Henneboel				
					appd.	09.12.09	Koch				
					norm						
					d-old		13K1IP3A		dwg no: 13K1A3024 part no: SEE TABLE		
	4 x b	Ä5187	28.04.2014	Lehm.							DIN- A3
	a	Original									sh: 1
	rev.	description	date	name							

Directive 2002/95/EC RoHS compliant

CONEC