



Connectors > Rectangular Connectors > Standard Rectangular Connectors > Rectangular Connectors: 6-Way Plug



Connector Product Type: **Connector Assembly**  
Connector & Housing Type: **Plug**  
Mating Alignment: **With**  
Mating Alignment Type: **Keyed**  
Mating Retention: **With**

[All Rectangular Connectors: 6-Way Plug \(23\)](#)

Features

Product Type Features

Connector Seal & Plug Type	Triple-Seal
Connector Shell Size	06
Connector Product Type	Connector Assembly
Connector & Housing Type	Plug
Connector System	Wire-to-Wire
Insertion Force Type	Normal
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Columns	3
Number of Signal Positions	6
Number of Cavities	6
Number of Power Positions	6
Contacts Preloaded	Yes
Number of Positions	6
Number of Rows	2



Electrical Characteristics

Operating Voltage	400 VAC
-------------------	---------

Body Features

Connector & Keying Code	A
Connector Seal Color	Natural
Seal Material	Fluorosilicone
Cable Exit Angle	180°
Seal Type	Grommet Seal, Interfacial Seal
Primary Product Color	Red

Contact Features

Contact Size	Size 22
Contact Type	Pin
Contact Retention Within Housing	With
Contact Current Rating (Max)	5 A

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Strain Relief	Without
Mating Alignment	With
Mating Alignment Type	Keyed
Mating Retention	With
Mating Retention Type	Button Latch

Housing Features

Housing Material	Composite
Shell Material	Composite
Centerline (Pitch)	2.54 mm[.1 in]

Dimensions

Row-to-Row Spacing	2.54 mm[.1 in]
Compatible Insulation Diameter Range	.71 – 1.37 mm[.028 – .054 in]

Usage Conditions

Operating Temperature Range	-55 – 175 °C[-67 – 347 °F]
-----------------------------	----------------------------

Operation/Application



Shielded	No
Circuit Application	Power & Signal

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Octamethylcyclotetrasiloxane (D4) (.5% in In Component part) Decamethylcyclopentasiloxane (D5) (.5% in In Component part) Dodecamethylcyclohexasiloxane (D6) (.5% in In Component part) <b>Article Safe Usage Statements:</b> Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 245°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

D369-P66-AP0

Connector Assembly, Plug, Crimp, Wire-to-Wire, Normal, 6 Position, DEUTSCH 369, Rectangular Wire & Cable Connectors & Housings



TE Part # YD369-B66-AS500000  
369 6 WAY PANEL MNT REC, 90 PCB TIN, SKT

TE Part # YD369-B66-AS400000  
369 6 WAY PANEL MNT REC, 90 PCB GOLD,SKT

TE Part # D369-R66-AS0  
369 6 WAY REC, NO CONTACTS, SKT

TE Part # CAT-D369-G66  
PCB Mount Receptacle: 6-Way Inline

TE Part # YD369-B66-AS000000  
369 6 WAY PANEL MNT REC, NO CONTACTS,SKT

Also in the Series | DEUTSCH 369

PCB Headers & Receptacles(91)

Rectangular Power Connectors(403)

Standard Rectangular Connectors(358)

Wire-to-Board Headers & Receptacles (91)

Customers Also Bought

TE Part #394441-E  
SRCA 1,27 2 F 1 IDC22 137 E1 094 1,27 TR

TE Part #2348771-2  
HD MATEnet SWS

TE Part #2-1617088-7  
3SAM6154N2 = 3SAM FULL SIZE LA

TE Part #0660-206-1282  
CONT PIN

TE Part #2348770-3  
HD MATEnet - COVER FOR SWS


TE Part #4-1617758-9  
FCB-205-0224L=M83536/2-024L

TE Part #8-320383-3  
TERMINAL,SOLIS R 2 1/4

TE Part #1-1718333-1  
2POS MOS REC COD A



TE Part #9-2354261-1  
HD MATEnet 1+2 REC HSG ASSY,  
GRP C



TE Part #CT88203001  
ASC114894ACK0066

Documents

Product Drawings

369 6 WAY PLUG, NO CONTACTS, PIN

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_D369-P66-AP0\_A\_c-d369-p66-ap0-a.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_D369-P66-AP0\_A\_c-d369-p66-ap0-a.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_D369-P66-AP0\_A\_c-d369-p66-ap0-a.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English