



4

3

2

1

used for: D-SUB COMBINATION



cable dimensions

Notes:

1. Plating mating side:

Inner conductor: min. 50µ" hard gold over min. 50µ" nickel

Outer Conductor: min. 30µ" hard gold over min. 50µ" nickel

2. Usable Cabel RG 179B/U, 187A/U

3. Impedance: 75 Ohm

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

				tolerance			scale: 5:1	
rev.	description	date	name	1999	date		material:	copper alloy
				drawn	05.05.	Barcinski	title: COAXIAL CONTACT FEMALE 75 OHM Inner conductor for solder termination outer conductor for crimp or solder termination	
				appd.	05.05.	Mickenbecker		
				norm				
				d-old				
							dwg no:	CAD/ REL.14
							13K1IP4A	DIN-A
							product no:	132J30029X

4

3

2

1

sh: 1/1