



Connectors > Rectangular Connectors > Rectangular Contact Inserts



Rectangular Connector Insert Type: **Contact Insert**

Contact Type: **Socket**

Pole Configuration: **24+PE**

Features

Product Type Features

Rectangular Connector Insert Type	Contact Insert
-----------------------------------	----------------

Electrical Characteristics

Power Circuit Voltage	400 V
-----------------------	-------

Body Features

Primary Product Color	Gray
-----------------------	------

Contact Features

Contact Type	Socket
Pole Configuration	24+PE

Packaging Features

Packaging Method	Box
Packaging Quantity	5

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2020 (205) Does not contain REACH SVHC



Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | HDC HSB

Insertion & Extraction Tools(2)

Rectangular Contact Inserts(8)

Customers Also Bought

TE Part #ZPF000000000201129
732-8052-31 WA

TE Part #ZPF000000000203708
DMC-M 99-10 PC

TE Part #CZ6862-000
HEX40-AC-45-25-A12-3

TE Part #ZPF000000000202094
DMC-M 0402 AW 01

TE Part #ZPF000000000203398
DMC-MR 30-23 PC

TE Part #ZPF000000000203399
DMC-MR 30-23 PD

TE Part #ZPF000000000202098
732-8052-18 WA

TE Part #225398-6
CONNECTOR, BNC DUAL CRIMP JACK

Documents



CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_7-1103641-1_E_c-7-1103641-1-e.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_7-1103641-1_E_c-7-1103641-1-e.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_7-1103641-1_E_c-7-1103641-1-e.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Agency Approvals

Agency Approval Document

English