



Technical specification:

Rated voltage:	24 V
Insulation resistance: IEC 60512	$\geq 100 \text{ M}\Omega$
Pollution degree: IEC 60664-1	3/2
Degree of protection: IEC 60529	IP 67, in mated condition
Temperature range: IEC 60664-1	$-30^\circ\text{C} \dots +80^\circ\text{C}$
Mating cycles: IEC 60512-9a	≥ 100


Materials:

Contact:	CuZn
Contact plating:	Nickel, gold plated
Contact carrier:	TPU, UL 94
Coupling screw:	CuZn, nickel plated
Moulding body:	TPU, UL 94, grey

Contact assignment:



Part no:	Description:
41-01304	SAL - DN - 7/8 - RSA5.3

DO NOT ALTER CAD DRAWING BY HAND Directive 2002/95/EC RoHS compliant	Index: a 05.04.11 VF Ä3941 data sheet revised			 dim. in mm		title: Male connector 7/8" axial, DeviceNet, terminal resistor	
			date	name			
				drawn	06.11.08	Mankopf	dwg no: 41K1A380
				appd.	06.11.08	Fromm	
	general tolerance: 0 ± 0,50mm 0,0 ± 0,25mm 0,00 ± 0,10mm					part no: see table	
	THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH						