

SERIES 48 - 12MM MINIATURE SEALED ELECTRO-MECHANICAL

This rugged multi-option sealed pushbutton series offers the utmost in choices of mounting styles, colors, terminations, bezels, lighting and momentary or alternate-action switching. The Series 48 offers all these options in one compact package size.

APPLICATIONS:

- Office equipment
- Medical equipment
- Industrial machinery
- Outdoor controls
- Mass transportation
- Food processing equipment



KEY FEATURES:

- Momentary or Maintained action
- Gold contacts
- Seven button colors
- Choice of LED colors (or non-illuminated versions)
- Solder or PC terminals

- Panel sealed to IP67 (Threaded Bush)
- Plastic bezel/ housing
- Raised button
- Snap action (see SA12 series)

Ordering Information:

Series:	Module Type:	Switch Function:	Switch Termination:	Bezel Type:	Led:	Button Color:	Mounting Type:	Voltage Resistor: If Blank*/\$
48 Gold Contact	1	Momentary	Solder	RB Round, Black	N None	RD Red	B Bushing	05 5V Forward
T	2	Maintained	Solder	SB Square, Black*	R Red	GR Green	S Snap-fit	T
	5	Momentary	PC	T	G Green	BK Black	T	
	6	Maintained	PC		Y Yellow	BL Blue		
	T				A Amber	YL Yellow		
					B Blue	OR Orange		
					W White	WH White		
			48					

- * Current limiting resistor maybe required to limit LED forward current to 20mA
- ^{\$} Other integrated LED voltages can be provided upon request depending on project volume
- * A setup charge maybe required for the Square Bezel

PRODUCT DRAWINGS


THREADED BUSH


SNAP-FIT







THREADED BUSH









SNAP-FIT









BUTTON HEIGHT

	FREE POSITION	MAINTAINED
WITH LED	7.51 [0.296]	6.00 [0.236]
NO LED	8.19 [0.323]	6.67 [0.263]

PANEL CUT-OUT





Mechanical Characteristics:

SPST-NO-DB (FORM X)

Button Travel (Nom):

[2.3] .09

Operating Force (Nom):

[3N] 306g

Contact Bounce (Nom):

1 ms

Panel Thickness:

Bushing Mounting:

[0.5-3.0] .02-.12

Snap-Fit Mounting:

[1.3-3.0] .05-.12

Nut Torque (Max):

[6 kgf-cm] 5.2 lb-in

Hardware:

Threaded Bush - Supplied with Panel Seal and Hex Nut in bags with the product packaging.

Snap-Fit - Panel Seal supplied fitted to the switch

ENVIRONMENTAL SPECIFICATIONS

Actuator Ingress Protection:

IP67 (Threaded Bush)

Operating Temperature:

[-40°C to +85°C] -40°F to + 185°F

ELECTRICAL SPECIFICATIONS

Current Rating (resistive):

48 (Momentary)

250mA@ 12VDC, 100K Cycles 150mA@ 28VDC, 150K Cycles 100mA @ 48VDC, 100K Cycles 10mA@ 12VDC, 1 Million Cycles

48 (Maintained)

50K Cycles Nominal

Dielectric Strength:

1,000 VAC

Insulation Resistance:

1G Ohm

Contact Resistance:

50m Ohms