



Part Number : [1202530583](#)
Product Description : Contrinex Inductive Sensor, M18 Fully Stainless Steel, 20mm Operating Distance, Non-embeddable, PNP, NO, 3-pin M8 Connector, 63.5mm Housing Length
Series Number : 120253
Status : Active
Product Category : Inductive and Photoelectric Sensors
Engineering Number : DW-AS-713-M18-002



Documents & Resources

Specifications
[1202530577-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Part Details

General

Status	Active
Category	Inductive and Photoelectric Sensors
Series	120253
Description	Contrinex Inductive Sensor, M18 Fully Stainless Steel, 20mm Operating Distance, Non-embeddable, PNP, NO, 3-pin M8 Connector, 63.5mm Housing Length
IP Rating	IP68, IP69K
Product Name	Contrinex
Type	Inductive
UPC	191130070183

Electrical

Output	NO
Polarity	PNP
Switching Frequency	≤ 200 Hz

Physical

Connection	Connector (M12, 4-pin)
Length	63.5mm
Material - Housing	Stainless Steel
Material - Sensing Face	Stainless Steel
Mounting Style	Non-embeddable
Operating Distance	20mm
Output	NO
Sensor Housing Size	M18
Temperature Range - Operating	-25° to +85°C