



Wire Protection & Management > Cable Glands > Plastic Cable Glands Without Locknut



Cable Gland Product Type: **Cable Gland**  
Cable Gland & Accessory Style: **Standard Threaded**  
Primary Product Material: **PA 6**  
Clamping Diameter Range: **3 – 7 mm**  
Primary Product Color: **Black**

[All Plastic Cable Glands Without Locknut \(240\)](#)

Features

Product Type Features

|                               |                   |
|-------------------------------|-------------------|
| Cable Gland Product Type      | Cable Gland       |
| Cable Gland & Accessory Style | Standard Threaded |
| Sealable                      | Yes               |

Body Features

|                          |       |
|--------------------------|-------|
| Primary Product Material | PA 6  |
| Primary Product Color    | Black |

Dimensions

|                         |          |
|-------------------------|----------|
| Clamping Diameter Range | 3 – 7 mm |
| Outer Thread Size       | NPT 3/8" |
| Thread Length           | 15 mm    |

Usage Conditions

|                             |                           |
|-----------------------------|---------------------------|
| Operating Temperature Range | -20 – 100 °C[-4 – 212 °F] |
|-----------------------------|---------------------------|

Industry Standards



|                        |          |
|------------------------|----------|
| UL Flammability Rating | UL 94V-2 |
| IP Rating              | IP68     |

Packaging Features

|                  |     |
|------------------|-----|
| Packaging Method | Bag |
|------------------|-----|

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                               |
|-----------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                     |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                     |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                       |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2025 (247)<br>Candidate List Declared Against: JAN 2023 (233)<br>Does not contain REACH SVHC |
| Halogen Content                               | Not Yet Reviewed for halogen content                                                                                          |
| Solder Process Capability                     | Not reviewed for solder process capability                                                                                    |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought





TE Part #1SNG601156R0000  
EP-SG-NPT38-BL-B



TE Part #20011426-00  
830M1-0500 Triaxial 500g Tape Reel  
150pc



TE Part #1SNG609028R0000  
ENBR-WG-NPT38-BL-A



TE Part #1SNG607030R0000  
EP-LN-NPT38-BL-A



TE Part #2-2176407-1  
3560 91K 1%




TE Part #42373-2  
187 FASTON REC 20-16 AWG TPBR



TE Part #BAT-HLD-014-THM  
Battery Holder 2023 THM Bulk Pack



TE Part #218034-005  
55A0811-12-9



TE Part #2119783-1  
RAM TRANSPORTATION COLLAR



TE Part #BAT-HLD-013-SMT-TR  
Hldr for CR2032 Battery, SMT, T&R Pkg

Documents

Product Drawings  
EP-SG-NPT38-BL-A

English

CAD Files  
3D PDF

3D

Customer View Model  
ENG\_CVM\_CVM\_1SNG601153R0000\_A.2d\_dxf.zip

English

Customer View Model  
ENG\_CVM\_CVM\_1SNG601153R0000\_A.3d\_igs.zip

English

Customer View Model  
ENG\_CVM\_CVM\_1SNG601153R0000\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages



Catalog - ENTRELEC Cable Glands

English

Agency Approvals

UL

English

UL

English